

2-Port Compact USB KVM Switch w/Audio and Cable

MODEL NUMBER: **B004-VUA2-K-R**



Description

The B004-VUA2-K-R is a 2-port Compact USB KVM Switch with optional audio and microphone switching function. It allows you to access, control, boot and reboot two USB-enabled computers from a single console (keyboard, monitor and mouse). The independent audio/mic switching function allows an uninterrupted audio experience - you can continue listening to audio even when you switch to the other computer.

It includes innovative, easy-to-use KVM Switcher Software for Windows and Macintosh platforms. A small client application facilitates your KVM switching operations such as computer selection, hot key sequence programming, auto-scanning, auto-scan delay time programming, independent or simultaneous audio/computer switching and more. Compatible with all major operating systems.

Features

- Fast, easy switching via keyboard hot keys, push buttons or software
- Plug-and-play setup - no software required
- Hot-swap capability allows easy addition or removal of computers without powering down the switch or other computers
- Speaker and microphone connections allow sharing of audio components between systems (standard 3.5 mm audio connections)
- Independent audio switching allows you to listen to audio from one computer while switching to the other computer
- Supports video resolutions up to 2048 x 1536 (standard 15-pin VGA connectors)
- Supports Microsoft® IntelliMouse® and the scrolling wheel on most mice]
- Compact design saves desk space
- Does not require an AC adapter
- Compatible with all major operating systems
- Includes two, 6ft Cable Kits

Highlights

- Fast, easy switching via keyboard hot keys, push buttons or software (not required)
- PC and Mac compatible
- Allows sharing of audio components between systems; listen to music from one computer while switching to the other computer
- Compact design saves desk space
- No AC adapter required
- (x2) 6ft USB KVM Cable kits and (x2) 6ft 3.5mm Audio Cable kits included
- Compatible with all major operating systems

Applications

- Use this KVM switch when accessing two USB-equipped computers with one monitor, keyboard and mouse.

System Requirements

- Console: VGA, SVGA or Multisync Monitor, USB Keyboard and USB Mouse
- Computers: VGA, SVGA or Multisync Monitor Port and USB Port
- Audio (Optional): Speakers with standard 3.5 mm Connectors and a computer with 3.5mm ports
- Compatible with all major operating systems

Package Includes

- Compact 2-port USB KVM Switch with Audio
- (2) 6ft USB KVM Cable Kits and (2) 6ft 3.5mm Audio Cable Kits
- CD-ROM with KVM Switcher Software

Specifications

- Owner's Manual with Warranty Information

OVERVIEW	
Users	1
Console	No
Max CPU	2
PHYSICAL	
Color	Black
LCD Monitor (in.)	Not Applicable
LCD Monitor (cm)	Not Applicable
ENVIRONMENTAL	
Storage Temperature Range	-4° to 140° F (-20° to 40° C)
Operating Temperature	32° to 104° F (0° to 40° C)
BTUs	17.065
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, Software
IP Remote Access	No
CONNECTIONS	
Ports	2
PC/Server Connections	PS/2
Included KVM Cable (Equipment Side) - Connector 1	HD15 (Male)
Included KVM Cable (Equipment Side) - Connector 2	USB A (Male)
Included KVM Cable (Equipment Side) - Connector 3	(x2) 3.5mm (Male)
Local Console Ports - Port 1	HD15 (Female)
Local Console Ports - Port 2	(x2) USB A (Female)
Local Console Ports - Port 3	(x2) 3.5mm (Female)
SPECIAL FEATURES	



Cat5 KVM Switch	No
CERTIFICATIONS	
Certifications	FCC, CE, RoHS Compliant
NIAP-Certified Secure	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>