

# 1U Rack-Mount Console with 19-in. LCD, Short-Depth

MODEL NUMBER: **B021-000-19-SH**



## Description

Tripp Lite's B021-000-19-SH 1U Rackmount Console is the ideal solution for specialized vehicle projects, including rescue services and military specific applications. It can be mounted in as little as a 19" deep rack and features an integrated 19" LCD display, ( max resolution of 1280x1024), full 104-key keyboard and touch pad, all in a 1U rackmountable housing. This console is designed for use with a server or a KVM switch with PS/2 or USB console connectors. Constructed of heavy-duty steel housing.

## Features

- Mounts in 19" to 30" deep cabinets
- Full 19" LCD display screen, 104-key keyboard, touchpad
- Max resolution of 1280x1024
- 100-240V Auto Sensing External AC Adapter, 6-ft.
- Includes Console-to-KVM 6-ft. cable kit for use with PS/2 or USB KVMs or Servers
- Single rail, ball bearing slides
- Constructed of heavy-duty steel housing

## Highlights

- Short-depth console mounts in cabinets with a minimum depth of 19"
- Designed for use with KVMs or Servers that have PS/2 or USB connectors
- 19" LCD Screen with 1280x1024 resolution
- 100-240V Auto Sensing External Power Supply

## Applications

- Specialized mobile cabinets, 19" - 30" depth

## Package Includes

- 1U 19" KVM Console Short-Body
- External AC Power Adapter
- Console-to-KVM Switch Cable
- Owner's Manual

## Specifications

OVERVIEW	
Users	1
PRODUCT OVERVIEW	
Product Overview	1U 19" KVM Console Short-Body



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>PHYSICAL</b>	
Color	Black
<b>ENVIRONMENTAL</b>	
Power Consumption (Watts)	48 Watts Max
<b>COMMUNICATIONS</b>	
IP Remote Access	No
<b>CONNECTIONS</b>	
Connector A	HD15 (FEMALE)
Ports	0
PC/Server Connections	VGA; USB; PS/2
<b>SPECIAL FEATURES</b>	
Cat5 KVM Switch	No
<b>CERTIFICATIONS</b>	
Certifications	FCC Part 15 Class A, CE, EN 60950-1
NIAP-Certified Secure	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>