

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0334820601](#)  
**Status:** **Active**  
**Overview:** [MX150™ Sealed and Unsealed Connector System](#)  
**Description:** MX150™ Sealed Male Connector, Dual Row, 6 Circuits, Polarization A, without Connector Position Assurance, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-33472-100 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-33472-100-FR (PDF)</a>
<a href="#">Product Specification PS-33472-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">33482</a>
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	<a href="http://ewcap.uscarteams.org">http://ewcap.uscarteams.org</a>
Overview	<a href="#">MX150™ Sealed and Unsealed Connector System</a>
Product Name	MX150™
UPC	756054494455

**Physical**

Circuits (maximum)	6
Circuits Detail	6
Color - Resin	Black, Natural
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	9.651/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

**Electrical**

Current - Maximum per Contact	22.0A
-------------------------------	-------

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100, AS-33472-100-FR
Product Specification	PS-33472-000
Sales Drawing	SD-33482-0002, SD-33482-061



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Contains SVHC(2015 June 15): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Compliant

**Search Parts in this Series**

[33482](#) Series

**Mates With**

[33472](#) Female Dual Row Sealed Connector

**Use With**

[33000](#) MX150™ Tin (Sn) Male Terminal, [33011](#) Gold (Au) Male Terminal, [34345-0001](#) MX™ 150 Cavity Plug Sealed, MX150™ Backshell [34950-0640](#) , [34950-0620](#)