



## range introduction

Established range of plugs and adaptors. The established names of Safetyplug™, Toughplug™ and Duraplug® strengthen MK's reputation for high quality products with the accent on safety and quality.

## Safetyplugs

## Toughplugs

## NON STANDARD



646 WHI

647 CHA

655 BLK

646 CHA

647 WHI

655 ORG

647 CHA

655 D8 RED

<b>646 WHI</b>	<b>10</b>
<b>646 CHA</b>	<b>10</b>
FITTED WITH 13 AMP FUSE	
<b>646/3 WHI</b>	<b>10</b>
FITTED WITH 3 AMP FUSE	
<b>645 NIP</b>	<b>100</b>
SECRET SCREW FOR SAFETYPLUG AND TOUGHPLUG	
<b>644 ZIC</b>	<b>10</b>
KEY FOR SECRET SCREW	

<b>647 WHI</b>	<b>10</b>
<b>647 CHA</b>	<b>10</b>
FITTED WITH 13 AMP FUSE	

<b>655 WHI</b>	<b>10</b>
FITTED WITH 13 AMP FUSE	
<b>655/3 WHI</b>	<b>10</b>
FITTED WITH 3 AMP FUSE	
<b>655 BLK</b>	<b>10</b>
<b>655 ORG</b>	<b>10</b>
<b>655 RED</b>	<b>10</b>
FITTED WITH 13 AMP FUSE	
<b>655 D8 WHI</b>	<b>10</b>
<b>655 D8 RED</b>	<b>10</b>
MARKED 'HOSPITAL PROPERTY'. FITTED WITH 13 AMP FUSE	

See page 194 for spare fuse links.  
BS 1363 Pt.1: 1995

See page 194 for spare fuse link  
For use only with MK non-standard  
13 amp socket outlets.

See page 194 for spare fuse link  
BS 1363/A Pt.1: 1995

BS1363 Pt1: 1995 (where relevant)

technical hotline +44 (0)1268 563720

portable power | wiring devices

## Rubber Plugs

## Round Pin Plugs

## Plug Adaptors

13 AMP

ROUND PIN



PF133 WHI



PF133 ORG



PF133 BLK



P53 BLK



P153 BLK



505 WHI



515 WHI



641 WHI



690 WHI



692 WHI



696 WHI



698 PPK

**PF133 WHI**  
**PF133 ORG**  
**PF133 BLK**  
FITTED WITH  
13 AMP FUSE

10  
10  
10

**P53 BLK**  
5 AMP  
**P153 BLK**  
15 AMP

10  
10

**502 WHI**  
2 AMP  
**505 WHI**  
5 AMP  
**515 WHI**  
15 AMP  
RESILIENT COVER

**639 WHI**  
2 AMP FUSED  
**641 WHI**  
5 AMP FUSED  
**643 WHI**  
15 AMP  
FITTED WITH 5 AMP FUSE

10  
10  
10  
10  
10  
10

**690 WHI**  
13 AMP  
WITH 1 X 13A  
AND 1 COMBINED 16A UNIVERSAL  
AND GERMAN TYPE 2P+E  
SOCKET OUTLET  
FUSED 13 AMP

BS 1363 Pt.3: 1995

5

**692 WHI**  
13 AMP  
WITH 3 X 13A SOCKET OUTLETS  
FUSED 13 AMP  
**696 WHI**  
13 AMP  
WITH 2 X 13A SOCKET OUTLETS  
UNFUSED

**698 PPK**  
13 AMP  
WITH 1 X 1A  
SHAVER SOCKET OUTLET  
FUSED 1 AMP

BS 1363 Pt.3: 1995

With rubber cover and ABS/  
Polycarbonate base.

Colour coded sleeves  
on the pins.

Available with alternative fuse  
ratings to special order only.  
BS 1363/A Pt.1: 1995

**P53 BLK**  
Manufactured in rubber.

**P153 BLK**  
With rubber cover and ABS/  
Polycarbonate base.  
BS 546: 1950

See page 194 for spare  
fuse links to BS 646.  
BS 546: 1950