

Micro-USB Charge-and-Sync Cable M/M - Left-Angle Micro-USB - 30/24 AWG - 1 m (3 ft.)

StarTech ID: USBAUB1MLA



This 30/24 Micro-USB cable features 24 AWG wire, to provide the full power you need to charge your mobile devices faster.

Plus, the left-angled Micro-USB connector is great for charging your mobile devices in a car, or for accessing your mobile device while it's connected to a wall charger or computer.

Provide full charging power to your mobile devices

Different phones and tablets require specific amounts of power to charge efficiently. A phone might only require 1.0A of power while a tablet may need 2.4A of power.

This 30/24 Micro-USB cable is designed to deliver full power to your mobile devices so that all of your devices can charge at the expected speed.

Connect with ease

The left-angled Micro-USB connector lets you connect to ports that are difficult to reach, which is perfect for charging your car-mounted mobile devices. Even while you're charging your mobile device, you can use it to text, work or game, without the cable getting in the way.

The angled connector also prevents the cable from bending awkwardly or from straining too much to make a connection. It offers a more natural fit at the connection point, preventing unnecessary stress and damage to the cable and device port.

Charge and sync your USB mobile devices

Replace the Micro-USB cable that came with your mobile device, or keep one as a spare while traveling so that your mobile devices will be ready to use while you're on the road.

The USBAUB1MLA 1-meter cable is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Applications

- Charge and sync your Micro-USB mobile devices
- Replace the cable that came with your Micro-USB device or keep one as a spare while traveling

Features

- Provide full charging power to your Micro-USB mobile devices
- Connect to your device even in hard to reach areas and tight spaces
- Guaranteed reliability with our lifetime warranty

Technical Specifications

Warranty	Lifetime
Cable Length	1000 mm [39.4 in]
Color	Black
Connector Style	Straight to Left Angle
Product Length	1000 mm [39.4 in]
Product Weight	29 g [1 oz]
Wire Gauge	24/30 AWG
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Connector Plating	Nickel
Type and Rate	USB 2.0 - 480 Mbit/s
Connector A	1 - USB A (4 pin) Male
Connector B	1 - USB Micro-B (5 pin) Male
Package Quantity	1
Shipping (Package) Weight	33 g [1.2 oz]
Included in Package	1 - 1m Left-Angle Micro-USB 2.0 Charging Cable for Tablets and Phones

Certifications, Reports and Compatibility

