

acer
explore beyond limits™

TOUCH MORE



Aspire Switch 10

SW5-012


*Premium design 2-in-1 detachable
Stunning 10.1" HD IPS Display
Hybrid Storage Solution
Extended productivity*



Acer recommends Windows 8.



FREEDOM



SPECIFICATIONS

Aspire Switch 10 SW5-012



Product views	1 HD webcam 2 10.1" touch display with 1280 x 800 HD resolution ¹ 3 Dual speakers 4 Keyboard hooks	5 Keyboard connector 6 Microphone 7 MicroSD™ card slot 8 Micro USB port 9 Micro HDMI® port	10 DC-in jack for AC adapter 11 Multi-gesture touchpad 12 FineTip keyboard 13 Headphone/speaker jack 14 Power button	15 Volume button 16 Home button 17 USB 2.0 port (on keyboard)	
Operating system¹	Windows 8.1 32-bit Free Upgrade to Windows 10				
CPU and chipset¹	Intel® Atom™ processor Z3735F (2M Cache, up to 1.83 GHz)				
Memory^{1, 2, 3}	Single-channel DDR3L SDRAM support: 2 GB of onboard DDR3L system memory				
Display^{1, 4}	10.1" display with IPS (In-Plane Switching) technology, HD 1280 x 800 resolution, high-brightness LED-backlit TFT LCD with integrated multi-touch, supporting 5-finger touch, Zero Air Gap technology (Direct Bonding)				
	16:10 aspect ratio	Wide viewing angle	Super-slim design	Mercury free, environment friendly	
Graphics¹	Intel® HD Graphics with 3D graphics hardware acceleration				
Audio	Two built-in stereo speakers	Built-in digital microphone			
Storage⁶	<ul style="list-style-type: none"> 32GB eMMC (Tablet) + 500GB Slim SATA HDD in Keyboard microSD™ Card (up to 128GB) 				
Webcam¹	Video conferencing: Acer Crystal Eye HD webcam with 1920 x 1080 resolution and 1080p Full HD audio/video recording				
Wireless and networking^{1, 6, 7}	WLAN <ul style="list-style-type: none"> Operates at 2.4 GHz 802.11b/g/n wireless LAN 		WPAN <ul style="list-style-type: none"> Bluetooth® 4.0 		
Privacy control¹	Trusted Platform Module (TPM) solution				
Dimensions and weight⁸	Dimensions 261.6 (W) 177.1 (D) x 8.9 (H) mm (10.3 x 6.97 x 0.35 inches)		Weight 0.585 kg (1.29 lbs.) with 2-cell battery pack 1.17 kg (2.58 lbs.) with 2-cell battery pack, pad and dock 1.2 kg (2.65 lbs.) with 2-cell battery pack, pad and dock with hard drive		
Power adapter and battery	Power adapter 2-pin 18 W AC adapter		Battery <ul style="list-style-type: none"> 22 Wh 5910 mAh 3.8 V 2-cell Li-polymer battery pack Battery life up to 8 hours 		
Input and control	Keyboard: 83-/84-/87-key, 95% full-size Acer FineTip keyboard with international language support Touchpad: Multi-gesture touchpad, supporting two-finger scroll and pinch. Swipes access charms, application commands, Microsoft Precision Touchpad Certification Control Keys: Volume up and down keys, Windows key				
Sensors	Accelerometer (G-sensor)	E-compass	Gyroscope	Ambient light sensor	
Windows Store Apps⁹	Content <ul style="list-style-type: none"> Amazon® Kindle CANAL TOUCH eReadingNow Hulu Hulu Plus iQIYI iStoryTime Library LeTV 	<ul style="list-style-type: none"> Love Wallpaper HD MagV NetEase Cloud Reading Netflix Next Issue Magazines Sohu Video TuneIn Radio VcRead Zinio™ 	Games <ul style="list-style-type: none"> Microsoft Solitaire Collection Taptiles In-House <ul style="list-style-type: none"> Acer Explorer Acer Hover Access (FHD model only) Lifestyle <ul style="list-style-type: none"> Accuweather 	<ul style="list-style-type: none"> Backpackers Booking.com CTRIP Travel EZTABLE Select Rakuten Recipes StumbleUpon Yandex.Maps Yandex.Money 	Productivity <ul style="list-style-type: none"> Evernote™ Touch Shopping <ul style="list-style-type: none"> Amazon® eBay® Meituan Rakuten Gateway
Windows Desktop Apps⁹	Content <ul style="list-style-type: none"> LOVEFiLM® web link Spotify In-House <ul style="list-style-type: none"> Acer Docs Acer Media Acer Photo Acer Portal 	<ul style="list-style-type: none"> Acer Remote Files Acer Video Player Accessory Store Identity Card Live Updater Quick Access Recovery Management 	Lifestyle <ul style="list-style-type: none"> Agoda web link Booking.com web link Hao123 web link Yandex web link Yandex.Disk Desktop 	Productivity <ul style="list-style-type: none"> Office 365 Search <ul style="list-style-type: none"> Bing Security <ul style="list-style-type: none"> PC Manager 	Shopping <ul style="list-style-type: none"> Amazon® 1 Button app eBay Worldwide Gomaji Tools <ul style="list-style-type: none"> Launch Manager Nero BackItUp Soluto
Options and accessories	2-pin 18 W AC adapter	Micro USB 2.0 to USB 2.0 cable			
Warranty	One-year International Travelers Warranty (ITW)				

- Specifications vary depending on model.
- Shared system memory may be allocated to support graphics, depending on system memory size and other factors. Actual system memory available to the operating system will be reduced by any memory used by the graphics solution and resources required by the operating environment.
- Memory speed may vary, depending on the CPU, chipset or memory fitted.
- All brands and product names mentioned herein include trademarks of their respective companies and are used solely to describe or identify the products.
- 1 GB is 1 billion bytes, 1 TB is 1000 GB. Actual formatted capacity is less and may vary depending on preloaded materials and operating environment. Acer Recovery Management uses a portion of the stated hard disk capacity as dedicated backup space.
- Actual throughput may vary depending on network conditions and environmental factors such as network traffic or overhead, building construction and access point settings.
- Subject to availability.
- Weight may vary depending on product configuration, vendor components, manufacturing variability, and selected options.
- Bundled software may vary depending on hardware configuration, OS and regional availability.
- The images, pictures, and illustrations are for illustration purposes only, and do not necessarily represent the exact products, services, or ideas in the context they are found in.

In a continuing effort to improve the quality of our products, information in this document is subject to change without notice. Images shown are only representations of some of the configurations available for this model. Availability may vary depending on region. As a phenomenon known to thin-film transistors (TFTs), liquid crystal displays (LCDs) commonly exhibit a small number of discoloration dots, as so-called "non-conforming pixels." This phenomenon is a limitation of TFT LCD technology, not a product defect, and as such is not covered by Acer's warranty.

© 2014. All rights reserved.

Microsoft and Windows are registered trademarks of Microsoft Corporation. Intel, Intel Core, Core Inside, Pentium, Pentium Inside and Celeron are trademarks of Intel Corporation in the U.S. and other countries.

About Acer

Established in 1976, Acer is a *hardware + software + services* company dedicated to the research, design, marketing, sale and support of innovative products that enhance people's lives. Acer's product offering includes PCs, displays, projectors, servers, tablets and smartphones — tools our customers need to explore beyond limits and experience more. Acer employs 7,400 people and ranks No. 4 for total PCs globally (IDC 2013). Revenues for 2013 reached US\$12.02 billion. Please visit www.acer.com for more information.

acer
explore beyond limits™