



Screwdriver Style Soldering Tip

Model: 720



American Beauty Tools - Paragon Soldering Tip - Model 720

Description

Any tradesman worth their salt will tell you, "If you want a job to turn out right, you've got to start with the right materials." We incorporate that philosophy into our soldering tips. Every American Beauty Paragon soldering tip starts with a solid core of Tellurium Copper. We know of no better alloy that combines the characteristics of high thermal conductivity with corrosion resistance required for effective soldering.

Subsequently, all tips then undergo a multitude of processes that include iron cladding, nickel plating, chrome coating and pre-tinning. Each process is conducted in a clean environment to prevent contamination and ensure proper material adherence. The end result is a soldering tip that provides optimal performance over a long life span.

Features and Benefits

All American Beauty Paragon Soldering Tips are **Lead Free** and **RoHS compliant** making them perfectly suitable for your greener environment.

Paragon Iron-Clad Lead-Free Soldering Iron Tips consistently outperform and outlast ordinary soldering iron tips many times over. **Plug-style tip design** provides for superior heat transfer and easy cleaning.

Click on **Related Parts** link to reveal other tip styles with matching diameter to this tip. American Beauty routinely **stocks** all of the most popular styles of soldering tips.

Technical Specifications

| | |
|---|-------------------|
| RoHS Compliant | Yes |
| Tip Configuration | Screwdriver |
| Tip Diameter | .25 in |
| Tip Length | 2.25 in / 5.72 cm |
| Width of Working Area | .16 in / 0.41 cm |
| Thickness of Working Area | .045 in / 0.11 cm |
| Tapered Distance of Working Area | .75 in / 1.91 cm |
| Understanding Tip Measurements | Explanation |
| Country of Origin | CR |
| Package Length | 2.50 in / 6.35 cm |
| Package Width | 1.00 in / 2.54 cm |
| Package Height | .25 in / 0.64 cm |
| Shipping Weight | .05 lbs / 0.02 kg |
| Warranty Policy | Details |

Similar Products

The following products are related (similar model but different specifications, etc.) to Model 720 featured on this page:

| Model | Product Name | Price |
|-------|---|---------|
| 701 | Turned Down Screwdriver Style Soldering Tip | \$14.00 |
| 703 | Turned Down Chisel Style Soldering Tip | \$14.00 |
| 704 | Chisel Style Soldering Tip | \$14.00 |
| 709 | Diamond Style Soldering Tip | \$14.00 |
| 714 | Turned Down Screwdriver Style Soldering Tip | \$14.00 |
| 715 | Screwdriver Style Soldering Tip | \$14.00 |
| 716 | Turned Down Screwdriver Style Soldering Tip | \$14.00 |

| Model | Product Name | Price |
|--------------|--|--------------|
| 724 | Conical Style Soldering Tip | \$14.00 |
| 739 | Needle Point Conical Style Soldering Tip | \$14.00 |
| 749 | Oversized Chisel Style Soldering Tip | \$18.00 |