



25 Watt, 3/16" Pencil-Style Soldering Iron Model: 3110-25



Description

The little guy that really packs a punch! Designed in the same fashion as our heavy-duty soldering irons, these pencil-style irons are certainly not your average hobby iron. Referred to as production-ready, these irons repeatedly perform hard soldering applications, day in and day out. The combination of intense heat and unmatched durability yields a pencil iron that can proudly be called an American Beauty and makes a versatile tool in any maintenance and repair operation. *(Stand Included)*

Features and Benefits

Ni-Chrome Compression Wound Heating Elements are proven to be the most reliable heating element for maintaining soldering temperature in production environments.

Paragon Iron-Clad Lead-Free Soldering Iron Tips consistently outperform and outlast ordinary soldering iron tips many times over.

Plug-style tip design provides for superior heat transfer and easy cleaning.

Modular construction allows for easy replacement of consumable parts allowing for tools to last for generations.

Technical Specifications

User Manual	Download
Is a stand included?	Yes
Product Length	6.5 in / 16.51 cm
Maximum Temperature	875 °F / 468.33°C
Wattage	25 watts
RoHS Compliant	Yes
Tip Diameter	.1875 in
Standard Tip Style	Screwdriver
Is a high voltage version (220-240VAC) available?	No
Country of Origin	US
Package Length	9.75 in / 24.77 cm
Package Width	2.00 in / 5.08 cm
Package Height	2.00 in / 5.08 cm
Shipping Weight	.55 lbs / 0.25 kg
Warranty Policy	Details

Replacement Parts

The following products can be used as replacements for Model 3110-25 featured on this page:

Model	Product Name	Price
3916	Replacement Handle/Cord set for Pencil Irons	\$20.50
618	Screwdriver Style Soldering Tip	\$13.00
9010-25	Replacement 25 Watt Compression-Wound Heating Element	\$43.60

Accessories

The following products can be used as Accessories for Model 3110-25 featured on this page:

Model	Product Name	Price
480	'One-Pass' Solder Tip Cleaner	\$16.00
481	'Well-Type' Solder Tip Cleaner	\$16.00
485-8C	Dri-Wick Desoldering Braid in Thumb-Wheel Dispenser	\$6.00

Model	Product Name	Price
571	Soldering Iron Stand	\$9.40
610	Diamond Style Soldering Tip	\$13.00
625	Conical Style Soldering Tip	\$13.00
643	Chisel Style Soldering Tip	\$13.00
HS-A	Heat Sink - Micro Alligator Clip	\$10.50
HS-B	Heat Sink - Alligator Clip	\$10.50
HS-C	Heat Sink - Alligator Clip w. Barrel	\$10.50
SS-8	Solder Sucker (3 oz)	\$10.50

Similar Products

The following products are related (similar model but different specifications, etc.) to Model 3110-25 featured on this page:

Model	Product Name	Price
3110-30	30 Watt, 3/16" Pencil-Style Soldering Iron	\$71.20
3110-35	35 Watt, 3/16" Pencil-Style Soldering Iron	\$71.20
V36GM3	40 Watt Industrial Grade Soldering Station	\$180.00