

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0190340005**  
**Status:** **Active**  
**Overview:** Snap Plugs and Receptacles  
**Description:** InsulKrimp™ Snap Plug, for 18-22 AWG Wire, 22.61mm Length

**Documents:**

3D Model  
Drawing (PDF)  
Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)  
RoHS Certificate of Compliance (PDF)

**Agency Certification**

CSA LR18689  
UL E152602

**General**

Product Family Quick Disconnects  
Series 19034  
Crimp Quality Equipment Yes  
Insulated Partial  
MolexKits Yes  
Overview Snap Plugs and Receptacles  
Product Name InsulKrimp™  
Type Snap Plug  
UPC 800753047327

**Physical**

Barrel Type Closed  
Flammability 94V-0  
Gender Male  
Glow-Wire Compliant No  
Insulation PVC  
Lock to Mating Part None  
Material - Metal Copper  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Net Weight 1.158/g  
Orientation Straight  
Packaging Type Bag  
Tab Thickness N/A  
Tab Width N/A  
Wire Insulation Diameter 3.60mm max.  
Wire Size AWG 18, 20, 22

**Electrical**


Voltage - Maximum 600V

**Material Info**

Old Part Number A-269X

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
Sales Drawing SD-19034-004



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(2014  
December 17): No

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

19034 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
found by selecting the products below.  
Crimp Height Specifications are then  
contained in the Application Tooling  
Specification document.*

**Global**

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640050300</u>
PremiumGrade™ Hand Crimp Tool	<u>0640010100</u>
Hand Crimp Tool	<u>0640010300</u>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640050100</u>

This document was generated on 10/13/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**