

## Warranty

### WE'RE HERE TO HELP YOU! NEED ASSISTANCE SETTING UP THIS PRODUCT?

Make sure you:

1. Use the live chat at [www.iogear.com](http://www.iogear.com) to try and solve any issues you may be having with the product.
2. Visit the Tech Info Library/FAQ on [www.iogear.com](http://www.iogear.com) (under the Support tab).
3. Call the 24/7 tech support line at 1-866-946-4327 (U.S. only) or 949-453-8782.

### Warranty Information

This product carries a 3 Year Limited Warranty. For the terms and conditions of this warranty, please go to <http://www.iogear.com/support/warranty> or call 1-866-946-4327.

Register online at <http://www.iogear.com/register>

### Important Product Information

Product Model \_\_\_\_\_  
Serial Number \_\_\_\_\_

## Contact

### IOGEAR Inc.

Address: 23 Hubble, Irvine, CA 92618 USA  
Toll Free: 866-94IOGEAR  
Phone: 949-453-8782  
Web site: [www.iogear.com](http://www.iogear.com)  
Email: [support@iogear.com](mailto:support@iogear.com)

## About Us



**FUN**  
IOGEAR offers connectivity solutions that are innovative, fun, and stylish, helping people enjoy daily life using our high technology products.

**GREEN**  
IOGEAR is an environmentally conscious company that emphasizes the importance of conserving natural resources. The use of our technology solutions helps reduce electronic waste.

**HEALTH**  
IOGEAR supports healthy and fit lifestyles. By integrating products with the latest scientific developments, IOGEAR's solutions enhance the life of end-users.



## Quick Start Guide

### 2/4-Port USB Cable KVM Switch

GCS22U / GCS24U  
PART NO. Q1090 / Q1094

## Package Contents

- 1 x 2/4-Port USB Cable KVM Switch
- 1 x Quick Start Guide
- 1 x Warranty Card


## System Requirement

- Computers with two open USB ports and a VGA (HDDB15) connection
- Windows 98, 98SE, ME, 2000 or higher, XP, Vista
- Mac OS 9.0 or greater
- Sun Solaris work station
- Linux, UNIX and other USB supported systems\*
- \*Additional drivers and support may be needed

## Overview

### Start Here!

1. Console USB Mouse Port
2. Console VGA Monitor Port
3. LEDs
4. Console USB Keyboard Port
5. Remote Switch Button
6. CPUs KVM Cables



## Installation

### Step 1

Please make sure your computers and monitor are powered off before you start.

### Step 2

Connect the VGA cable from your monitor to the console VGA monitor port.



### Step 3


Connect your USB keyboard and mouse to the console USB keyboard port and console USB mouse port.



## Installation

### Step 4

Connect a set of your molded KVM cable to each of your computers – VGA cable to the VGA output and USB cables to open USB ports from your computer.



### Final Step

Turn on your computers.

## Port Switching

Simply press the remote port switching button to switch to the next port.

## LED Indication

LED will light up in green showing the port that is selected.