

Rackmount Mixers

ULTRALINK PRO MX882

Ultra-Flexible 8-Channel Splitter/Mixer



- Ultra-low noise 8 in/2 out line mixer and 2 in/8 out line splitter
- Each channel can operate independently in mixer or splitter mode
- Usable as 6 in/6 out level matching amplifier or direct injection box
- Converts levels between -10 dBV and +4 dBu
- Extremely wide bandwidth from 5 Hz to 200 kHz for highest signal integrity
- 6 mono in, 6 mono out, 2 main inputs and 2 outputs
- 1/8-segment input/output level meters for all channels
- High-quality components and exceptionally rugged construction ensure long life
- 3-Year Warranty Program*
- Conceived and designed by BEHRINGER Germany

The MX882 is definitely one piece of gear every audio engineer and musician should always have close at hand. This ultra-flexible, little “life saver” has proven invaluable time and time again in live performances, professional recording studios, CD and digital production facilities, and a variety of other scenarios where the show simply had to go on! The MX882 is ideal for distributing a stereo signal to several outputs (splitter mode); combining multiple signals into a stereo output (mixer mode), or adapting signal levels of signals for a variety of audio applications (buffer amplifier). The ULTRALINK PRO MX882 can perform all of these functions easily and simultaneously – it is quite literally, the audio version of a “Swiss Army Knife”.



ULTRALINK PRO MX882

Ultra-Flexible 8-Channel Splitter/Mixer



It's a Mixer – It's a Splitter


Basically, the MX882 consists of 6 mono channels, which can be used either as a splitter or as a mixer. For instance, a stereo program source can be connected via the Main Inputs, and then routed to any of the mono channels set to Split mode. For our example, we'll use Channel 1 with the Split/Mix switch in the out (Split) position. Adjust the Channel 1 Balance/Pan control to set how much of the Left and Right Main Input signal is routed to the Channel 1 mono Output XLR. And you can do the same thing with all 6 of the MX882 channels.

In Mix mode, the input signals from any, or all, of the MX882's 6 channels can be mixed to the stereo Main Output, with their individual Balance/Pan controls determining the signal's placement within the stereo image (Pan). It is advantageous that when operating in Mix mode, the stereo Main Input signal is automatically sent to the Main Outputs – allowing you to combine a total of up to 8 individual signals. The mono Input signals are still sent to their mono outputs, which means each channel can also be used as an individual matching amplifier. The Level controls for the corresponding channels enable the user to adapt the levels at will, with a maximum gain of +15 dB. Levels used in home-recording can easily be converted into studio levels (+4 dBu), and vice versa.

Typical Applications

As we mentioned above, the ULTRALINK PRO MX882 is one of the most flexible systems of its type. Below are just a few of the applications the multitasking MX882 can accommodate:

- Keyboard or drum submixer
- Distribution amplifier for PA systems, dance clubs, theatres, churches, hotels, communication systems, etc.
- Add-on module for mixer channels
- Add-on module for FX and monitor paths
- Level translator from -10 dBV to +4 dBu, or vice versa



Rackmount Mixers

ULTRALINK PRO MX882

Ultra-Flexible 8-Channel Splitter/Mixer



A Must-Have for Your Bag of Tricks

As you can see, the incredibly-flexible MX882 is one hand piece of gear – and just might save your next gig or recording session. At its ultra-affordable price tag, you'll want 2 or 3 for your studio, and a couple more for your live rack. Get down to your [BEHRINGER](#) dealer – or get your ULTRALINK PRO MX882 online today!

You Are Covered

We always strive to provide the best possible Customer Experience. Our products are made in our own [MUSIC Group](#) factory using state-of-the-art automation, enhanced production workflows and quality assurance labs with the most sophisticated test equipment available in the world. As a result, we have one of the lowest product failure rates in the industry, and we confidently back it up with a generous [3-Year Warranty program](#).



Rackmount Mixers

ULTRALINK PRO MX882

Ultra-Flexible 8-Channel Splitter/Mixer



Rackmount Mixers

ULTRALINK PRO MX882

Ultra-Flexible 8-Channel Splitter/Mixer



For service, support or more information contact the BEHRINGER location nearest you:

Europe
MUSIC Group Services UK
Tel: +44 156 273 2290
Email: CARE@music-group.com

USA/Canada
MUSIC Group Services NV Inc.
Tel: +1 702 800 8290
Email: CARE@music-group.com

Japan
MUSIC Group Services JP K.K.
Tel: +81 3 6231 0454
Email: CARE@music-group.com

MUSIC Group accepts no liability for any loss which may be suffered by any person who relies either wholly or in part upon any description, photograph, or statement contained herein. Technical specifications, appearances and other information are subject to change without notice. All trademarks are the property of their respective owners. MIDAS, KLARK TEKNIK, TURBOSOUND, BEHRINGER, BUGERA and DDA are trademarks or registered trademarks of MUSIC Group IP Ltd. © MUSIC Group IP Ltd. 2015 All rights reserved.

