



Technical Specifications



MICROPHONO PP400

Ultra-Compact Phono Preamp

MICROPHONO PP400

Ultra-Compact Phono Preamp

- Converts your phono signal to a line level signal
- State-of-the-art phono preamp to accommodate all magnetic pickups
- Dedicated RCA and ¼" TRS output connectors
- DC 12 V adapter included
- High-quality components and exceptionally rugged construction ensure long life
- Conceived and designed by BEHRINGER Germany

Specifications

Input

| | |
|------------------|------------------|
| Type | RCA connector |
| Impedance | approx. 47 kW |
| Max. input level | -23.5 dBV @ 1kHz |

Output

| | |
|-------------------|-----------------------------------|
| Type | RCA and ¼" TRS, stereo connectors |
| Impedance | approx. 50 W |
| Max. output level | +11.5 dBV @ 1 kHz |

System Specifications

| | |
|-----------------------|----------------------------|
| Frequency response | RIAA |
| THD | 0.06% typ. @ -40 dBu/1 kHz |
| Gain | 35 dB |
| Signal-to-noise ratio | 68 dBu @ 0 dBu, A-weighted |
| Input sensitivity | 5.3 mV @ 1 kHz |

Power Supply

| | |
|------------------|--|
| Mains connection | external power supply, 12 V $\overline{\text{=}}$ / 150 mA |
|------------------|--|

Mains Voltage

| | |
|-------------------|--------------------|
| USA/Canada | 120 V~, 60 Hz |
| China/Korea | 220 V~, 50 Hz |
| U.K./Australia | 240 V~, 50 Hz |
| Europe | 230 V~, 50 Hz |
| Japan | 100 V~, 50 - 60 Hz |
| Power consumption | approx. 1.5 W |

Dimensions/Weight

| | |
|------------------------|--|
| Dimensions (H x D x W) | approx. 1 ¼ x 4 x 2 ½" approx. 32 x 103 x 64 mm |
| Weight | approx. 0.40 lbs / 0.180 kg |

BEHRINGER is constantly striving to maintain the highest professional standards. As a result of these efforts, modifications may be made from time to time to existing products without prior notice. Specifications and appearance may differ from those listed or illustrated.

TECHNICAL SPECIFICATIONS AND APPEARANCES ARE SUBJECT TO CHANGE WITHOUT NOTICE AND ACCURACY IS NOT GUARANTEED. BEHRINGER, KLARK TEKNIK, MIDAS, BUGERA, AND TURBOSOUND ARE PART OF THE MUSIC GROUP (MUSIC-GROUP.COM). ALL TRADEMARKS ARE THE PROPERTY OF THEIR RESPECTIVE OWNERS. MUSIC GROUP ACCEPTS NO LIABILITY FOR ANY LOSS WHICH MAY BE SUFFERED BY ANY PERSON WHO RELIES EITHER WHOLLY OR IN PART UPON ANY DESCRIPTION, PHOTOGRAPH OR STATEMENT CONTAINED HEREIN. COLORS AND SPECIFICATIONS MAY VARY FROM ACTUAL PRODUCT. MUSIC GROUP PRODUCTS ARE SOLD THROUGH AUTHORIZED FULLFILLERS AND RESELLERS ONLY. FULLFILLERS AND RESELLERS ARE NOT AGENTS OF MUSIC GROUP AND HAVE ABSOLUTELY NO AUTHORITY TO BIND MUSIC GROUP BY ANY EXPRESS OR IMPLIED UNDERTAKING OR REPRESENTATION. THIS MANUAL IS COPYRIGHTED. NO PART OF THIS MANUAL MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING AND RECORDING OF ANY KIND, FOR ANY PURPOSE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF MUSIC GROUP IP LTD. ALL RIGHTS RESERVED.

© 2013 MUSIC Group IP Ltd. Trident Chambers, Wickhams Cay, P.O. Box 146, Road Town, Tortola, British Virgin Islands