

Introducing SBPlus Self Laminating Wire and Cable Markers

SBPlus Self Laminating Wire and Cable Markers

KEY FEATURES

- More aggressive adhesive than the current SB product it replaces.
- Adhesive helps to prevent lift off in the most demanding applications.
- Clear base material allows the printing to remain more legible after over-lamination.

DESCRIPTIONS

Clear vinyl film with a permanent acrylic based adhesive, supplied with a white thermal transfer printable area, which is over-laminated upon application with the clear portion of the label.

APPLICATIONS

Used to identify commercial and industrial grade wire and cable products with an operating temperature range of -51C to +93C (-60F to +200F)

MECHANICAL

Clear over-lamination provides mechanical and splash fluid protection to the printed area of the label.

MATERIALS

Clear vinyl with a thermal transfer printable white area for printing.

PRODUCT OFFERING

Packaged on both 1" and 3" diameter cores. Quantity per package ranges from 10,000 labels per spool for the smallest sizes to 1,000 labels per spool for the largest sizes.

APPLICATION TOOLING

No special application tooling is required. Print using a qualified Tyco Electronics Thermal Transfer printer and ribbon.

PRODUCT INFORMATION



Available Sizes and Formats

Printer Model	Approved Ribbon	Certification
T208M	TMS-101-RIBBON-4RPSCE	UL 969
T212M	TMS-101-RIBBON-4RPSCE	UL 969
T308S	TMS-RJS-RIBBON-4RPSCE	UL 969
T312S	TMS-RJS-RIBBON-4RPSCE	UL 969
TE3012M	TMS-RJS-RIBBON-4RPSCE	UL 969
TE3112M	TMS-RJS-RIBBON-4RPSCE	UL 969
TE3124M	TMS-RJS-RIBBON-4RPSCE	UL 969



SBPlus Self Laminating Wire and Cable Markers

Part Numbering System



Available Sizes and Formats

Ordering Description	Package Quantity	Labels Across	Max Cable OD		(A) Label Width		(B) Label Height		(C) Printable Height		(D) Horizontal Repeat		(E) Vertical Repeat		(F) Web Width	
			mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches
SBP050100WE10	10,000	5	5.1	.20	12.70	0.500	25.40	1.000	8.50	0.330	16.80	0.600	31.00	1.222	86.00	3.384
SBP050143WE10	10,000	5	7.6	.30	2.70	0.500	36.50	1.437	12.70	0.500	16.80	0.662	42.20	1.661	86.00	3.384
SBP075094WE10	10,000	4	7.6	.30	19.10	0.750	23.90	0.940	9.50	0.375	20.30	0.800	28.60	1.125	85.10	3.350
SBP080150WE10	10,000	4	7.6	.30	20.30	0.800	38.10	1.500	12.70	0.500	22.90	0.900	44.50	1.750	94.90	3.736
SBP100143WE5	5,000	3	7.6	.30	25.40	1.000	36.50	1.437	12.70	0.500	27.90	1.100	42.20	1.661	87.30	3.436
SBP100225WE5	5,000	3	12.2	.48	25.40	1.000	57.20	2.250	19.10	0.750	27.90	1.100	66.70	2.625	87.30	3.436
SBP100375WE2.5	2,500	3	22.4	.88	25.40	1.000	95.30	3.750	25.40	1.000	27.90	1.100	101.60	4.000	87.30	3.436
SBPH100375WE2.5	2,500	1*	22.4	.88	25.40	1.000	95.30	3.750	25.40	1.000	N/A	N/A	28.60	1.125	100.30	3.950
SBP100594WE1	1,000	3	35.6	1.4	25.4	1.000	151.00	5.940	38.10	1.500	27.90	1.100	158.80	6.250	87.30	3.436
SBP100743WE1	1,000	3	35.6	1.4	25.40	1.000	188.90	7.437	38.10	1.500	27.90	1.100	195.30	7.688	87.30	3.436
SBP190319WE2.5	2,500	2	12.2	.48	48.30	1.900	81.00	3.190	19.10	0.750	50.80	2.000	87.40	3.440	105.10	4.138
SBP190594WE1	1,000	2	35.6	1.4	48.30	1.900	151.00	5.940	38.10	1.500	50.80	2.000	158.80	6.250	105.10	4.138
SBP200143WE2.5	2,500	2	7.6	.30	50.80	2.000	6.50	1.437	12.70	0.500	50.80	2.000	42.20	1.661	107.60	4.236
SBP200225WE2.5	2,500	2	12.2	.48	50.80	2.000	57.20	2.250	19.10	0.750	50.80	2.000	66.70	2.625	107.60	4.236
SBP200375WE2.5	2,500	2	22.4	.88	50.80	2.000	95.30	3.750	25.40	1.000	53.30	2.100	101.60	4.000	111.40	4.386
SBP200743WE	11,000	2	48.3	1.9	50.80	2.000	188.90	7.437	38.10	1.500	53.30	2.100	195.30	7.688	110.10	4.336

*One label across rotated format.

Options

Colors	Standard	White with clear tail
	Non-Standard	Red, Orange, Yellow, Green, Blue, Violet and Clear Tail

FOR MORE INFORMATION

Technical Support

Internet: www.tycoelectronics.com
E-mail: newproducts@tycoelectronics.com
USA: 1-800-522-6752
Canada: 1-905-470-4425
Mexico: 1-800-733-8926
C. America: 52-55-1106-0803
South America: 55-11-2103-6000
Hong Kong: 852-2735-1628
Japan: 81-44-844-8013
UK: 44-8706-080208

Tyco Electronics Corporation
Harrisburg, PA

tycoelectronics.com

Copyright 2008 Tyco Electronics Corporation
6-1773453-1 2.5M FP 12/2008
TE logo and Tyco Electronics are trademarks.



Tyco Electronics
Our commitment. Your advantage.