

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1502000002](#)
Status: **Active**
Overview: Ditto™ Wire-to-Wire Interconnects
Description: Ditto™ Genderless Crimp Terminal, Tin Brass, Preplated Tin, 24-26 AWG

Documents:

Drawing (PDF)	Test Summary TS-150170-0000 (PDF)
Product Specification PS-150170-0000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	150200
Application	Power
Comments	See Product Specification for maximum current rating by circuit size and AWG.
Crimp Quality Equipment	Yes
Overview	Ditto™ Wire-to-Wire Interconnects
Product Name	Ditto™
UPC	889056215657

Physical

Durability (mating cycles max)	25
Gender	Genderless
Material - Metal	Tin Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.156/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.05-1.50mm
Wire Size AWG	24, 26
Wire Size mm ²	N/A


Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	350V AC/DC

Material Info

Reference - Drawing Numbers

Product Specification	PS-150170-0000
Sales Drawing	SD-150200-0000
Test Summary	TS-150170-0000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[150200](#) Series

Use With

Ditto™ Genderless Crimp Housing [150170](#) , [150201](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Ditto Wing Genderless Interconnects Terminal, 24–26 AWG	0638278600
FineAdjust™ Applicator for	0639038500

Male and Female
Terminal Ditto™
Interconnects, 24-26
AWG

This document was generated on 03/08/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION