


BATTERIES

	NOMINAL VOLTAGE	NOMINAL CAPACITY	LENGTH	WIDTH	HEIGHT	WEIGHT	TERMINAL DETAILS	INTERNAL RESISTANCE	CHARGE CURRENT MAX	CCA AT 0°C	SHORT CIRCUIT	QTY PER BOX
BEG060075	6V	6.5Ah	151mm	34mm	94mm	1.2kg	B - T1	14mΩ	1.5A	N/A	350A	10
BEG060100	6V	10Ah	151mm	34mm	94mm	1.67kg	B - T1	10mΩ	4A	N/A	500A	10
BEG060120	6V	12Ah	151mm	50mm	94mm	1.85kg	B - T2	10mΩ	4.8A	N/A	600A	10
BEG120075	12V	8Ah	151mm	65mm	94mm	2.5kg	D - T1	20mΩ	3.2A	N/A	400A	8
BEG120120	12V	12Ah	151mm	98mm	95mm	4.4kg	D - T2	16mΩ	4.8A	N/A	600A	4
BEG120180	12V	17Ah	181mm	77mm	167mm	5.5kg	C - M5	16mΩ	6.8A	270A	850A	2
BEG120180A	12V	17Ah	181mm	77mm	167mm	5.7kg	C - M5*	16.5mΩ	5.1A	270A	850A	2
BEG120260	12V	24Ah	166mm	175mm	125mm	8.1kg	C - M5	12mΩ	9.6A	300A	1200A	1
BEG120330A	12V	33Ah	195mm	130mm	155mm	11kg	B - M6	10mΩ	9.9A	320A	850A	1
BEG120450	12V	45Ah	197mm	165mm	170mm	14.6g	C - M6	7.5mΩ	13.5A	350A	1050A	1
BEG120550	12V	55Ah	229mm	138mm	208mm	18.5kg	B - M6	5.8mΩ	14A	380A	1400A	1
BEG120700	12V	60Ah	258mm	166mm	206mm	24kg	C - M6	5mΩ	18A	550A	2100A	1
BEG120800	12V	75Ah	258mm	166mm	206mm	23.5kg	B - M6	5mΩ	20A	620A	2400A	1
BEG120900	12V	90Ah	306mm	169mm	210mm	30kg	B - M6	4mΩ	22A	680A	2650A	1
BEG121000	12V	90Ah	306mm	169mm	210mm	30kg	B - M6	5mΩ	25A	780A	2900A	1
BEG121200	12V	126Ah	410mm	176mm	227mm	38kg	B - M6	4.3mΩ	37.8A	1020A	2250A	1
BEG121500	12V	156Ah	482mm	170mm	240mm	47kg	B - M8	3.8mΩ	46.8A	1300A	2700A	1
BEG122000	12V	200Ah	520mm	238mm	218mm	65kg	E - M8	<36mΩ	50A	1670A	5400A	1

T1 = Faston Tab No.187 (4.8mm) T2 = Faston Tab No.250 (6.3mm)
 * = BEG120180A has a horizontal maintained M5 terminal

NB: Total height does not allow for terminal bolt when screwed into battery terminals (Relevant for screw terminal batteries)



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS



+44 (0)1638 716101
 info@camdenboss.com
 www.camdenboss.com

We operate a constant improvement policy,
 our products are subject to change without notice.

Ver 1.1
 Iss 6

