

BATTERIES

	NOMINAL VOLTAGE	NOMINAL CAPACITY	LENGTH	WIDTH	HEIGHT	WEIGHT	TERMINAL DETAILS	CHARGE CURRENT MAX	CCA AT 0°C	SHORT CIRCUIT	QTY PER BOX
BEV061600	6V	180Ah	306mm	168mm	220mm	26.6kg	M8	50A	1014A	5000A	1
BEV120075	12V	9Ah	151mm	65mm	94mm	2.8kg	D-F1	1.5A	-	275A	8
BEV120120	12V	12Ah	151mm	98mm	95mm	4.4kg	D-T2	4.8A	-	600A	4
BEV120180	12V	17Ah	181mm	77mm	167mm	5.9kg	M5	6.8A	144A	950A	2
BEV120260	12V	24Ah	166mm	175mm	125mm	9.2kg	M5	9.6A	228A	1300A	1
BEV120330	12V	30Ah	196mm	131mm	160mm	10.3kg	M6	7A	258A	1100A	1
BEV120330A	12V	33Ah	195mm	130mm	155mm	11kg	M6	9.9A	-	850A	1
BEV120450	12V	40Ah	197.5mm	165.5mm	170mm	14.7kg	M6	12A	345A	900A	1
BEV120550	12V	55Ah	228mm	138mm	208mm	18.5kg	M6	14A	466A	1700A	1
BEV120650	12V	77Ah	272mm	165mm	188mm	21.7kg	M8	20A	602A	2400A	1
BEV120700	12V	75.6Ah	350mm	167mm	179mm	22.5kg	M6	24A	557A	1900A	1
BEV120800	12V	82Ah	260mm	168mm	211mm	25.5kg	M8	22A	664A	2650A	1
BEV121000	12V	90Ah	306mm	169mm	210mm	29kg	M8	25A	751A	2900A	1
BEV121100	12V	100Ah	330mm	171mm	214mm	32kg	M8	27A	804A	3000A	1
BEV121200	12V	120Ah	410mm	176mm	224mm	36.5kg	M8	30A	951A	4200A	1
BEV121500	12V	150Ah	482mm	170mm	240mm	47kg	M8	40A	965A	4700A	1
BEV121600	12V	164Ah	530mm	209mm	214mm	54.2kg	M8	50A	985A	5400A	1

T1 = Faston Tab No.187 (4.8mm) T2 = Faston Tab No.250 (6.3mm)

NB: Total height does not allow for terminal bolt when screwed into battery terminals (Relevant for screw terminal batteries)

