



The Kärcher K4 Full Control pressure washer is a great addition to your tools. This product will help you achieve amazing results. Whether you are looking to clean your patio, car, wheelie bin, garden furniture, fencing and many other applications, the new full control system can help you find the right pressure setting, ensuring an optimal clean. Simply choose the correct spray lance, based on the surface you wish to clean, using the surface symbols on the spray lances as guides. Once you have chosen the lance you wish to use, simply twist the vario lance to find the correct pressure setting, guided by the LED display on the trigger gun. This new system will help you achieve the best possible clean for your home. This K4 model is perfect for tackling medium sized patios and cars and yet powerful enough to tackle tough dirt. With its long-life water-cooled motor, this model comes with a 3 year warranty. This pressure washer comes with a dirt blaster spray lance and a vario power spray lance.





### K4 Full Control

#### Technical data

Order No.	1.324-002.0	
EAN code	4054278045016	
Pressure	bar / MPa	20–130 / 2–13
Flow rate	l/h	420
Max. water feed temperature	°C	40
Power rating	kW	1,8
Weight without accessories	kg	11,42
Dimensions (L x W x H)	mm	397 x 305 x 584

#### Equipment

High-pressure gun	Full Control Trigger Gun
Vario Power spray lance	■
Dirt Blaster spray lance	■
High-pressure hose	m 6
Quick Connect on machine	■
Detergent application via	Plug and Clean system
Telescopic handle	■
Water-cooled motor	■
Soft bag	■
Integrated water filter	■

■ Included in delivery.

# Accessories for K4 Full Control 1.324-002.0



		Order No.		Dummy	Dummy	Dummy	Price	Description	
<b>Miscellaneous</b>									
Full Control Trigger Gun	1	2.643-634.0	■						■
Water filter	2	4.730-059.0	-						<input type="checkbox"/>
Replacement O-ring set	3	2.640-729.0	-						<input type="checkbox"/>
Adapter for garden hose connection	4	2.640-732.0	-						<input type="checkbox"/>
<b>High Pressure Replacement Hose with Anti-Twist system and Quick Connect system</b>									
H 10 Q PremiumFlex Anti-Twist	5	2.643-585.0	■						<input type="checkbox"/>
<b>High-pressure hose extension - System from 2008</b>									
High-pressure extension hose, 10 m, K3 - K7 (for gun model "Best").	6	2.641-710.0	-						<input type="checkbox"/>
High-pressure extension hose, 10m	7	2.641-708.0	-						<input type="checkbox"/>
High-pressure extension hose, 6 m, K3 - K7 (for gun model "Best").	8	2.641-709.0	-						<input type="checkbox"/>
<b>Connectors/Tap adaptors</b>									
Universal hose coupling	9	2.645-191.0	-						<input type="checkbox"/>
<b>Hoses &amp; Hose Reels/Trolleys</b>									
Connection Set for high-pressure cleaners	10	2.645-156.0	-						<input type="checkbox"/>
Indoor Hose Connection Set	11	2.645-258.0	-						<input type="checkbox"/>
PrimoFlex Hose: 20m	12	2.645-138.0	-						<input type="checkbox"/>
Premium Hose Reel HR 7.315 Kit 1/2"	13	2.645-164.0	-						<input type="checkbox"/>
<b>High-pressure hose replacement kit - from 1992</b>									
Adapter Set Extension Hose	14	2.643-037.0	-						<input type="checkbox"/>
Accessories kit quick connect *UK	15	2.642-301.0	-						<input type="checkbox"/>

■ Included in delivery. □ Available accessories.

# Accessories for K4 Full Control 1.324-002.0

**KÄRCHER**



		Order No.					Price	Description	
<b>Hard surface cleaners</b>									
PS 40 power swab surface cleaner	1	2.643-245.0						The Kärcher PS40 power scrubber comes with three integrated high-pressure nozzles giving you a powerful, reliable and time-saving solution for removing stubborn dirt on a variety of surfaces.	<input type="checkbox"/>
T 100 T-Racer	2	2.640-637.0						For the cleaning of flat surfaces without splashback, e.g. patios, terraces and walls made of stone and wood. Two rotating fan jet nozzles for increased cleaning power. Fast efficient, simple. Further Kärcher accessories can be connected to extension lances.	<input type="checkbox"/>
T 200 "T-Racer" surface and patio cleaner	3	2.641-361.0						T 250 T Racer. For cleaning flat surfaces (e.g. patios) and vertical surfaces (e.g. garage doors) without splash back. Features two rotating flat jet nozzles for better cleaning results.	<input type="checkbox"/>
T550 Patio Cleaner	4	2.643-251.0						The Kärcher T550 patio cleaner is our most powerful patio cleaner. Allowing you to clean large surface areas quickly. Included in this model is a detergent application feature.	<input type="checkbox"/>
T450 Patio Cleaner	5	2.643-214.0						The T450 Kärcher patio cleaner is a handy attachment for your Kärcher pressure washer. Twin-jet rotating arms allow you to clean areas like patios and decking faster and with great results.	<input type="checkbox"/>
T350 Patio Cleaner	6	2.643-252.0						The Kärcher T350 patio cleaner allows you to clean large areas quickly and efficiently, as well as being splash-free. This model includes adjustable cleaning pressure for different surfaces.	<input type="checkbox"/>
Spare nozzles accessories	7	2.643-338.0							<input type="checkbox"/>
Spare nozzles accessories T 300 / T 350	8	2.643-335.0							<input type="checkbox"/>
<b>Accessory kits</b>									
Window and conservatory cleaning set	9	2.640-771.0						Window and conservatory cleaning set includes soft flat brush, vario joint, 3-stage lance extension and squeegee. For cleaning and drying windows and conservatories.	<input type="checkbox"/>
Bike Cleaning accessory kit	10	2.643-551.0						The bike cleaning accessory kit from Kärcher is the perfect addition to your pressure washer to help you clean your motor bike. This kit help you achieve the perfect clean for your bike.	<input type="checkbox"/>
Car Cleaning Accessory Kit	11	2.643-554.0						The car cleaning accessory kit from Kärcher helps to transform your Kärcher pressure washer into the ultimate car cleaning tool. Including all the individual accessories you need for your car.	<input type="checkbox"/>
Wood Cleaning Accessory Kit	12	2.643-553.0						Kärcher's wood cleaning accessory kit is perfect for cleaning all wooden surfaces. From garden furniture to decking, this accessory kit will help you achieve the perfect clean.	<input type="checkbox"/>
<b>Brushes</b>									
WB 150 power brush	13	2.643-237.0						The Kärcher WB150 pressure washer brush is the perfect attachment for cleaning delicate surfaces such as car exteriors, motorbikes, glass, garage doors and conservatories.	<input type="checkbox"/>
WB60 Soft Surface Wash Brush	14	2.643-233.0						The Kärcher WB60 soft wash brush is a great addition to your Kärcher pressure washer to help you clean larger surfaces like cars, caravans, boats and conservatories.	<input type="checkbox"/>
WB100 Rotating Wash Brush	15	2.643-236.0						The Kärcher WB100 rotating wash brush is ideal for cleaning all smooth surfaces like paint, glass or plastic. It comes with a 180° joint making it infinitely adjustable.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories.



# Accessories for K4 Full Control 1.324-002.0

**KÄRCHER**



		Order No.					Price	Description	
Wheel Washing Brush	16	2.643-234.0						The Kärcher wheel washing brush is perfect for removing dirt and grime that accumulates on your wheel rims. With 360° degree cleaning enabling you to reach every angle of your wheels.	<input type="checkbox"/>
WB50 Soft Wash Brush	17	2.643-246.0						The Kärcher WB50 soft wash brush is suitable for thorough cleaning on all surfaces. With soft bristles that are gentle on all types of surfaces.	<input type="checkbox"/>
Brush best	18	4.762-380.0							<input type="checkbox"/>
Washing brush rigid	19	6.903-276.0						Standard Kärcher brush for pressure washers. Perfect for removing stubborn dirt and cleaning a wide variety of firm surfaces, from cars and caravans to windows and garden furniture.	<input type="checkbox"/>
<b>Spray lances</b>									
VP 145 Vario Power Jet	20	2.643-235.0						Vario-Power spray lance: spray lance with variable pressure control from low-pressure detergent jet to high-pressure jet. For use with K3 & K4 Machines.	<input type="checkbox"/>
Dirt Blaster Pressure Washer Lance	21	2.643-244.0						A powerful rotating nozzle ideal for removing stubborn dirt such as moss, algae and ground-in dirt, the Kärcher Dirt Blaster is the perfect attachment for tough cleaning jobs.	<input type="checkbox"/>
Angled spray lance	22	2.638-817.0						Extra-long angled spray lance (about 1 m) for easy cleaning of difficult to reach areas, e.g. roof gutters or vehicle underbodies.	<input type="checkbox"/>
Single Lance Extension	23	2.643-240.0						Extends spray lance by 0.5 m. For effective cleaning of difficult to reach areas. Suitable for all Kärcher accessories.	<input type="checkbox"/>
Flexible dirt blaster	24	2.639-001.0						Dirt Blaster for stubborn stains. With infinite angle adjustment of the dirt blaster head for easy and convenient cleaning of difficult-to-reach areas.	<input type="checkbox"/>
3-stage lance extension	25	2.639-722.0						3-stage lance extension set with four aluminium lances for difficult to reach areas. Variable extension to 90 cm, 1.30 m and 1.70 m.	<input type="checkbox"/>
Flexible spray lance	26	4.760-272.0						Flexible spray lance with adjustable high and low-pressure jet. Adjustable spray lance rotates through 180° for easier cleaning of difficult to reach areas.	<input type="checkbox"/>
Quadruple nozzle packaged 030 Premium Li	27	4.760-480.0						One all-purpose spray lance. Four types of jets in one spray lance: High-pressure fan jet, high-pressure pencil jet, low-pressure fan jet and dirt blaster. Simply twist the spray lance for switching.	<input type="checkbox"/>
Telescopic jet pipe	28	2.642-347.0						The Kärcher Telescopic jet pipe allows for easy cleaning of difficult to reach areas. With a shoulder strap and an ergonomically adjustable trigger gun, allowing you to reach up to 4m.	<input type="checkbox"/>
VP 145 Vario Power Jet	29	2.643-253.0						The Kärcher short Vario Power nozzle comes with pressure regulation and is adjustable 360°, making it ideal for cleaning difficult to reach areas. For use with K2 - K4 Machines.	<input type="checkbox"/>
<b>Special applications</b>									
Pipe cleaning set, 7.5 m	30	2.637-729.0						Pipe cleaning set with 7.5 m hose for clearing blockages in pipes, drains, downpipes and toilets.	<input type="checkbox"/>
Pipe cleaning set, 15 m	31	2.637-767.0						Pipe cleaning set with 15 m hose for clearing blockages in pipes, drains, downpipes and toilets.	<input type="checkbox"/>
Sand/wet blasting set	32	2.638-792.0						Sand and wet blasting set for removing rust, paint and stubborn dirt using Kärcher abrasive.	<input type="checkbox"/>
Vario joint	33	2.640-733.0						Vario joint, rotates 180° for cleaning difficult to reach areas. Connection: For connection between gun and accessory or extension lance and accessory.	<input type="checkbox"/>

■ Included in delivery. □ Available accessories.

