

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191930155**
Status: **Active**
Overview: VersaKrimp™ Terminals and Splices
Description: VersaKrimp™ Ring Tongue Terminal for 8 AWG Wire, Stud Size 1/4" (M6), Mylar Tape Carrier

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-015 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19193](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [VersaKrimp™ Terminals and Splices](#)
 Product Name VersaKrimp™
 Type Ring
 UPC 800753039506

Physical


Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 2.931/g
 Packaging Type Adhesive Tape on Reel
 Stud Size 1/4" (M6)
 Termination Interface: Style Crimp or Compression
 Wire Size AWG 8
 Wire Size mm² 6.60-10.50

Material Info

Old Part Number D-350-14T

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-015
 Sales Drawing SD-19193-016



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19193 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for VersaKrimp™ Ring Tongue Terminals, for Solid Copper or Steel Wire (Anti Rotation)	0190270117
ATP Crimp Dies for VersaKrimp™ Copper Ring Tongue Terminals And Butt	0190270111

Splices on Tape, 8
AWG
ATP Crimp Dies 0190270105
for VersaKrimp™
High Temperature
Nickel Plated Steel
Terminals on Tape, 8
AWG
ATP Crimp Dies 0190472000
for VersaKrimp™
Copper Ring Tongue
Terminals and Butt
Splices on Tape, 8
AWG, use with Tape
Crimp Module and
ATP-201 Press
ATP Crimp Dies 0190270120
for Versakrimp™ 8
AWG Ring Tongue
Terminals, for
Stripped Magnet or
Steel 6 AWG Wire

This document was generated on 03/02/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION