

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0561348000**
Status: **Active**
Overview: MicroClasp™ Wire-to-Board System
Description: 2.00mm Pitch Crimp Terminal 56134, Female, 22-26 AWG, Reel, Phosphor Bronze, for 51242/51353/51382 Housings

Documents:

[3D Model](#) [Packaging Specification SPK-56134-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	56134
Application	Signal
Crimp Quality Equipment	Yes
Overview	MicroClasp™ Wire-to-Board System
Product Name	MicroClasp™
UPC	800756190532


Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	36.000/mg
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.25-1.70mm
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-56134-001
Product Specification	RPS-51353-016, RPS-51382-015
Sales Drawing	SD-56134-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

56134 Series

Use With

51242 Dual Row Crimp Housing, 51353 Dual Row Crimp Housing, 51382 Single Row Crimp Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for 2.00mm Pitch Female Crimp Terminal	0639019600

Insertion Tool	<u>0011020022</u>
Hand Crimp Tool	<u>0638116300</u>
Extraction Tool	<u>0638132700</u>
T2 Terminator	<u>0639119600</u>

for 2.00mm Pitch
Female Crimp
Terminal

Japan

Description	Product #
--------------------	------------------

Applicator for M211A	<u>0574043000</u>
----------------------	-------------------

Bench Press, 18-22

AWG Wire

Side-Feed Applicator	<u>0574043200</u>
----------------------	-------------------

for Full-Auto Machine

This document was generated on 03/30/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION