

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192030052](#)  
**Status:** **Active**  
**Overview:** [High-Temperature Temp Terms Terminals and Splices](#)  
**Description:** Krimptite™ Temp-Term Ring Tongue Terminal for 14 to 16 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-015 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19203](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [High-Temperature Temp Terms Terminals and Splices](#)  
 Product Name Krimptite™, Temp-Terms  
 Type Ring  
 UPC 800753049734

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Plating Mating Tin  
 Net Weight 0.658/g  
 Packaging Type Adhesive Tape on Reel  
 Stud Size 10 (M5)  
 Wire Size AWG 14, 16  
 Wire Size mm² 1.00-2.50

**Material Info**

Old Part Number B-S-137-10T

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-015  
 Sales Drawing SD-19203-017



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per - ED/108/2014 (17 Dec 2014)

**Halogen-Free Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[19203 Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description  | Product #                  |
|--|----------------------------|
| Mini-Mac™ Applicator   | <a href="#">0638858100</a> |
| ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press | <a href="#">0190270055</a> |