

Male Vertical Surface Mount

- Contact datamate@harwin.com for tape & reel options.
- Optional pick and place cap.
- Mates with female connectors shown on pages 38, 39, 41, 42, 44 and 46 to 50.
- Gull wing SMT tails simplify inspection process.
- Board Mount provides PCB strain relief.



DATAMATE J-TEK

WITHOUT JACKSCREWS		WITH JACKSCREWS		WITH BOARD MOUNT																		
<p>Recommended PC Board Pattern</p>		<p>Recommended PC Board Pattern</p>		<p>Recommended PC Board Pattern</p>																		
<p>WITHOUT JACKSCREWS</p>		<p>WITH JACKSCREWS</p>		<p>WITH BOARD MOUNT</p>																		
<p>Calculation</p> <table border="1"> <tr> <td>A</td> <td>B + 12</td> </tr> <tr> <td>B</td> <td>Total no. of contacts - 2</td> </tr> <tr> <td>C</td> <td>B + 7</td> </tr> </table>		A	B + 12	B	Total no. of contacts - 2	C	B + 7															
A	B + 12																					
B	Total no. of contacts - 2																					
C	B + 7																					
<p>HOW TO ORDER</p> <p>M80 - 5 XX XX XX P</p>																						
<p>SERIES CODE</p>		<p>TOTAL NO. OF CONTACTS</p> <p>04 to 50</p> <p><small>Even numbers only</small></p>		<p>PICK AND PLACE CAP</p> <table border="1"> <tr> <td>BLANK</td> <td>No cap</td> </tr> <tr> <td>P</td> <td>Pick and place cap</td> </tr> </table>		BLANK	No cap	P	Pick and place cap													
BLANK	No cap																					
P	Pick and place cap																					
<p>TYPE</p> <table border="1"> <tr> <td>02</td> <td>With Jackscrews</td> </tr> <tr> <td>12</td> <td>With 3.5mm Board Mount</td> </tr> <tr> <td>13</td> <td>With 5mm Board Mount</td> </tr> <tr> <td>22</td> <td>Without Jackscrews</td> </tr> </table>		02	With Jackscrews	12	With 3.5mm Board Mount	13	With 5mm Board Mount	22	Without Jackscrews			<p>FINISH</p> <table border="1"> <tr> <td>05</td> <td>Gold</td> <td></td> </tr> <tr> <td>22</td> <td>Gold + Tin/Lead</td> <td></td> </tr> <tr> <td>42</td> <td>Gold + Tin</td> <td></td> </tr> </table>		05	Gold		22	Gold + Tin/Lead		42	Gold + Tin	
02	With Jackscrews																					
12	With 3.5mm Board Mount																					
13	With 5mm Board Mount																					
22	Without Jackscrews																					
05	Gold																					
22	Gold + Tin/Lead																					
42	Gold + Tin																					

All dimensions in mm.