


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0003092032](#)
Status: **Active**
Overview: [Standard .093" Pin and Socket Connectors](#)
Description: 2.36mm Diameter Standard .093" Pin and Socket Plug Housing, 3 Circuits, Single Row

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#)
[Product Specification PS-1396-002 \(PDF\)](#)
[Product Specification PS-43660-9999 \(PDF\)](#)
[Packaging Specification PK-1396-002 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	1396
Application	Power, Wire-to-Wire
Comments	17.0A max. can be achieved when housing is used with 42477 or 42478 terminals
Overview	Standard .093" Pin and Socket Connectors
Product Name	Standard .093"
UPC	800753614826
Physical	
Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-2
Gender	Plug
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.720/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.03mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
Current - Maximum per Contact	14.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Old Part Number	1396-P1
Reference - Drawing Numbers	
Packaging Specification	PK-1396-002
Product Specification	PS-02-09, PS-1396-002, PS-43660-9999
Sales Drawing	SD-1396-*, SD-1396-002



Series image - Reference only

EU ELV
Not Relevant

EU RoHS
Compliant
REACH SVHC
Not Contained Per -ED/79/2015 (17 December 2015)
Halogen-Free Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image
ELV Not Relevant

Search Parts in this Series
[1396 Series](#)

Mates With
[03-09-1031](#) , [03-09-1032](#) , [03-09-1033](#) ,
[03-09-1081](#) , [03-09-6032](#)

Use With
[1189](#) Crimp Terminals, [1190](#) Crimp Terminals, [1380](#) Male Crimp Terminals, [1381](#) Female Crimp Terminals, [1433](#) Crimp Terminals, [1434](#) Male Crimp Terminals, [1973](#) , [2151](#) , [2273](#) , [2870](#) , [2871](#) , [4272](#) , Link:4550, [6271](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION