


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192210244](#)
Status: **Active**
Overview: Battery Cable Lugs
Description: Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 3/8" (M9), Plated

Documents:

3D Model	Product Specification PS-19902-013 (PDF)
Drawing (PDF)	Product Specification PS-19902-017 (PDF)
Product Specification PS-19901-017 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011 (PDF)	



Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19221
Comments	Heavy Duty
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Battery Cable Lugs
Product Name	Battery Cable Lug
Type	Ring
UPC	800753062436

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	21.283/g
Packaging Type	Bag
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Stud Size	3/8" (M9)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	2/0

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Old Part Number	BCL-2038-PL
-----------------	-------------

Reference - Drawing Numbers

Product Specification	PS-19901-017, PS-19902-011, PS-19902-013, PS-19902-017
Sales Drawing	SD-19221-011

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

China RoHS

Search Parts in this Series

[19221](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0192840034
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008
Manual Putt Pump Hydraulic System, Die set required	0192860117

Die Set (large) for 0192900012
the HHLS Hydraulic
Crimper
Hydraulic Dieless 0638161700
Crimping Tool

This document was generated on 05/19/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION