

Description

The GM-ONE is an outstanding and feature-rich mid tower gaming case with a powerful cooling system. It comes with a wealth of great features such as 1 x USB 3.0 connectivity, angled transparent window side panel, tool-less 5.25" bays, 4 x 3.5" tool-less HDD and removable dust filter on the front panel and bottom. It has four 120mm fan, including 2 x 120mm front red LED fans and 1 x 120mm side red LED fan, the red LED lighting will keep your components cool whilst creating an excellent gaming feel. The GM-one is your best choice in affordable gaming cases.

Key Features

- **Black Interior** - Powder coated black interior, to aid with internal lighting
- **Supports Long Graphics Cards Up To 380mm** - With todays high end graphics cards increasing in length, this case will allow for most graphics cards to be used in your system, including in SLI or crossfire mode
- **4 x 120mm Fans inc.** - 2 x 120mm LED fans at the front of the case, 1 x 120mm LED fan on the side of the case and 1 x 120mm red bladed fan on the rear
- **Soft Touch Finish**
- **Space for up to 6 HDD Drives** - Up to 4 x 3.5" HDD and 2 x 2.5" HDD / SSD drives can be used.
- **Water Cooling Ready** - Pre-drilled water pipe holes on the rear of the case, with the grommets installed
- **Cable management** - The additional space behind the motherboard plate and the pre-cut holes allow for less clutter within you case to increase airflow
- **Stylish Side Window** - Angular side window to allow viewing of your PCs internal components
- **Carry Handle** - Allowing for gamers to transport their PC around to their friends or even their next LAN party.

Case Specifications

Form Factor: Midi Tower

Motherboard Support: ATX, Micro ATX, Mini ITX

PSU Support: Standard ATX

PSU Location: Bottom

Gaming Case: Yes

Water Cooling: Water Cooling Ready!
Grommeted Pipe Holes: **2**

Body Material: 0.5mm SECC Metal

Front Bezel Material: Plastic

Side Panel: Transprant Window / Vented

Internal Cable Management Depth: 23mm

External Bays: 1 x 5.25" External
1 x 3.5" External

Internal Bays: 4 x 3.5" Internal
2 x 2.5" Internal

Drive Bay Notes: 1 x 5.25" internal bay behind USB ports

Expansion Slots: 7 x Full Size

Cooling Front: 2 x 12cm Red LED Fans

Cooling Top: None

Cooling Rear: 1 x 12cm Black Fan

Cooling Side: 1 x 12cm Red LED Fan

Cooling Bottom: Filtered vent for PSU

IO Ports: 1 x USB 3.0
2 x USB 2.0
1 x HD Audio
1 x Microphone

GPU Max Length: 375mm

CPU Cooler Maximum Height: 157mm

Front Bezel Colour: Black

Body Colour: Black

System Cabinet Features: Carry Handle on top of case
USB3.0 port has USB2.0 additional header also
Bottom Mounted PSU

PSU Included: No

General Specifications

Manufacturer Part Number: GM-ONER

EAN Number: 5055492400178

Has Mains Plug: No

Colour: Black/Red

What's In The Box: Case
Screw Pack

Unit (Product)

Dimensions (mm): 205mm x 434mm x 457mm (W x H x D)

Packaging Dimensions (mm): 507mm x 252mm x 545mm (W x H x D)

Net Weight (KGs): 4.2 KGs

Gross Weight (KGs): 4.9 KGs