

Control Knobs

◀ RETURN

Manufacturer of  
**CLAMP KNOBS**

PRINT 

Clamp Knobs

Industrial Components

Military Knobs

Transilluminated Knobs

Transilluminated Specs

OEM Division

About Us

Catalog PDF

Distributors

Events

Press Releases

Govt NSN Stock


Distributor Login

Rep Login

ISO-9001 Certification



**Dimension Chart**



SHOW ENGLISH SIZES

**Description**

|                            |               |
|----------------------------|---------------|
| Knob Shape                 | Fluted Knob   |
| Knob Style                 | Lobe Knob     |
| Material                   | Thermoplastic |
| Insert                     | Steel Stud    |
| Insert or Stud Measurement | Metric        |

**Part-Family Table**

Click on the part number you choose for complete part description and prices

| <b>Part Number</b>           | <b>A</b> | <b>B</b> | <b>C</b> | <b>D</b> | <b>t</b> | <b>d2</b> |
|------------------------------|----------|----------|----------|----------|----------|-----------|
| <a href="#">05L-15S-M615</a> | 40       | 27       | 15       | 12       | M6       | 15        |
| <a href="#">05L-15S-M620</a> | 40       | 27       | 15       | 12       | M6       | 20        |
| <a href="#">05L-15S-M625</a> | 40       | 27       | 15       | 12       | M6       | 25        |
| <a href="#">05L-15S-M635</a> | 40       | 27       | 15       | 12       | M6       | 35        |
| <a href="#">05L-15S-M815</a> | 40       | 27       | 15       | 12       | M8       | 15        |
| <a href="#">05L-15S-M820</a> | 40       | 27       | 15       | 12       | M8       | 20        |
| <a href="#">05L-15S-M825</a> | 40       | 27       | 15       | 12       | M8       | 25        |
| <a href="#">05L-15S-M835</a> | 40       | 27       | 15       | 12       | M8       | 35        |
| <a href="#">05L-20S-M620</a> | 51       | 33       | 18       | 13       | M6       | 20        |
| <a href="#">05L-20S-M625</a> | 51       | 33       | 18       | 13       | M6       | 25        |

|                     |                                      |    |    |    |    |     |    |
|---------------------|--------------------------------------|----|----|----|----|-----|----|
| Contact Us          | <a href="#"><u>05L-20S-M630</u></a>  | 51 | 33 | 18 | 13 | M6  | 30 |
|                     | <a href="#"><u>05L-20S-M640</u></a>  | 51 | 33 | 18 | 13 | M6  | 40 |
| Request Information | <a href="#"><u>05L-20S-M820</u></a>  | 51 | 33 | 18 | 13 | M8  | 20 |
|                     | <a href="#"><u>05L-20S-M825</u></a>  | 51 | 33 | 18 | 13 | M8  | 25 |
| Request a Quote     | <a href="#"><u>05L-20S-M835</u></a>  | 51 | 33 | 18 | 13 | M8  | 35 |
|                     | <a href="#"><u>05L-20S-M840</u></a>  | 51 | 33 | 18 | 13 | M8  | 40 |
|                     | <a href="#"><u>05L-20S-M1020</u></a> | 51 | 33 | 18 | 13 | M10 | 20 |
|                     | <a href="#"><u>05L-20S-M1025</u></a> | 51 | 33 | 18 | 13 | M10 | 25 |
|                     | <a href="#"><u>05L-20S-M1035</u></a> | 51 | 33 | 18 | 13 | M10 | 35 |
|                     | <a href="#"><u>05L-20S-M1040</u></a> | 51 | 33 | 18 | 13 | M10 | 40 |
|                     | <a href="#"><u>05L-23S-M820</u></a>  | 60 | 40 | 22 | 16 | M8  | 20 |
|                     | <a href="#"><u>05L-23S-M830</u></a>  | 60 | 40 | 22 | 16 | M8  | 30 |
|                     | <a href="#"><u>05L-23S-M840</u></a>  | 60 | 40 | 22 | 16 | M8  | 40 |
|                     | <a href="#"><u>05L-23S-M1020</u></a> | 60 | 40 | 22 | 16 | M10 | 20 |
|                     | <a href="#"><u>05L-23S-M1030</u></a> | 60 | 40 | 22 | 16 | M10 | 30 |
|                     | <a href="#"><u>05L-23S-M1040</u></a> | 60 | 40 | 22 | 16 | M10 | 40 |
|                     | <a href="#"><u>05L-23S-M1220</u></a> | 60 | 40 | 22 | 16 | M12 | 20 |
|                     | <a href="#"><u>05L-23S-M1230</u></a> | 60 | 40 | 22 | 16 | M12 | 30 |
|                     | <a href="#"><u>05L-23S-M1240</u></a> | 60 | 40 | 22 | 16 | M12 | 40 |
|                     | <a href="#"><u>05L-30S-M1030</u></a> | 75 | 52 | 26 | 20 | M10 | 30 |
|                     | <a href="#"><u>05L-30S-M1040</u></a> | 75 | 52 | 26 | 20 | M10 | 40 |
|                     | <a href="#"><u>05L-30S-M1050</u></a> | 75 | 52 | 26 | 20 | M10 | 50 |
|                     | <a href="#"><u>05L-30S-M1230</u></a> | 75 | 52 | 26 | 20 | M12 | 30 |
|                     | <a href="#"><u>05L-30S-M1240</u></a> | 75 | 52 | 26 | 20 | M12 | 40 |
|                     | <a href="#"><u>05L-30S-M1250</u></a> | 75 | 52 | 26 | 20 | M12 | 50 |
|                     | <a href="#"><u>05L-30S-M1630</u></a> | 75 | 52 | 26 | 20 | M16 | 30 |
|                     | <a href="#"><u>05L-30S-M1640</u></a> | 75 | 52 | 26 | 20 | M16 | 40 |
|                     | <a href="#"><u>05L-30S-M1650</u></a> | 75 | 52 | 26 | 20 | M16 | 50 |

Distributor  
**STOCK**check✓

EHC Search:

Search



*Beyond control knobs . . . Components and assemblies within your reach.*



**Electronic Hardware Corporation** · 320 Broad Hollow Road, Farmingdale, NY 11735  
**Phone:** 631-752-1950 **Fax:** 631-752-1971 **www.ehcknobs.com** **Email:** sales@ehcknobs.com **1-800-752-1680**

*Associated Companies: EHC · SSI  
Facilities in New York, California, United Kingdom and Shanghai, China*

---

Privacy Statement ©Copyright 2009-2016 - All Rights Reserved

Graphics by Zuzzolo Graphics Inc  
Website Programming and Maintenance by Connetrix