

# M3 Portable

## External Hard Drive



The Maxtor M3 Portable External Hard Drive delivers handy portable storage. It is easy to take wherever you go, and has ample capacity of up to 4TB. The durable black design stands up to the rigors of daily use.

### PRODUCT HIGHLIGHTS

- Handy portable storage
- Durable black design
- SafetyKey™ protection for your data

### CONTENT

- M3 Portable External Hard Drive
- USB cable
- Quick Install Guide
- Software preloaded on the drive
- Electronic User Documentation (PDF)

### OPERATING SYSTEM

- Windows 10/8/7/Vista, Mac OS X 10.4.8 or later

### PERFORMANCE SPECIFICATION

- SuperSpeed USB 3.0 (Max): 5.0Gb/s

### ENVIRONMENTAL SPECIFICATION

- Temperature (operating): 5° to 40°C (41° to 104°F)
- Temperature (nonoperating): -20° to 65°C (-4° to 149°F)

### SOFTWARE

- AutoBackup personal backup solution
- Secure Drive for worry-free data security
- SecretZone™ can encrypt data on the device

### DRIVE WEIGHT & DIMENSION

- Weight (Max): 236g (4TB, 3TB), 169g (2TB), 151g (1TB), 141g (500GB)
- Size: 82mm W x 118.2mm L x 19.85mm H (max) (4TB, 3TB), 82mm W x 112mm L x 17.5mm H (max) (2TB, 1TB, 500GB)

### PACKAGED BOX WEIGHT & DIMENSION

- Weight: 373g (4TB, 3TB), 309g (2TB), 297g (1TB), 287g (500GB)
- Size: 137mm W x 185mm L x 38.5mm H

### MASTER CARTON DIMENSION

- 12 packaged drives
- Weight: 4.86kg (4TB, 3TB), 4.09kg (2TB), 3.93kg (1TB), 3.8kg (500GB)
- Size: 197mm W x 475mm L x 151mm H

### WARRANTY

- 3-year limited warranty

### TECH SUPPORT

- Online at [www.seagate.com](http://www.seagate.com)

### CAPACITIES SUMMARY

CAPACITY	MODEL NUMBER	PART NUMBER	EAN CODE	UPC CODE
4TB	STSHX-M401TCBM	HX-M401TCB/GM	7636490078491	763649091173
3TB	STSHX-M301TCBM	HX-M301TCB/GM	7636490078484	763649091166
2TB	STSHX-M201TCBM	HX-M201TCB/GM	7636490078477	763649091159
1TB	STSHX-M101TCBM	HX-M101TCB/GM	7636490078460	763649091142
500GB	STSHX-M500TCBM	HX-M500TCB/GM	7636490078507	763649091180

Seagate Technology LLC  
10200 South De Anza Boulevard, Cupertino, California 95014  
408-658-1000

© 2015 Seagate Technology LLC. All rights reserved. Seagate, Seagate Technology, the Spiral logo, Maxtor and Maxtor Logo are trademarks or registered trademarks of Seagate Technology LLC or one of its affiliated companies in the United States and/or other countries. All other trademarks or registered trademarks are the property of their respective owners. When referring to drive capacity, one gigabyte, or GB, equals one billion bytes and one terabyte, or TB, equals one trillion bytes. Your computer's operating system may use a different standard of measurement and report a lower capacity. In addition, some of the listed capacity is used for formatting and other functions, and thus will not be available for data storage. Actual data rates may vary depending on operating environment and other factors. The export or re-export of hardware or software containing encryption may be regulated by the U.S. Department of Commerce, Bureau of Industry and Security (for more information, visit [www.bis.doc.gov](http://www.bis.doc.gov)), and controlled for import and use outside of the U.S. Seagate reserves the right to change, without notice, product offerings or specifications. DS1879.1-1512US, December 2015

**Maxtor**®