

# PRODUCT SPECIFICATION

<b>Brand</b>	Avit
<b>Product Range</b>	Respiratory protection masks
<b>Catalogue number</b>	
<b>Date</b>	10/12/2010

## Range Description

Respiratory protection masks

## Features

- Active carbon layer protects against nuisance level odours e.g. brush/roller application of most domestic paints and varnish.
  - Valve reduces effort by making it easier to exhale.
  - Two point strap and adjustable nose clip for optimum fit.
  - Foam nose piece for extra comfort.
  - Colour coded straps and valve for easy identification
- 
- Protection against low level fine dust, oil or water based mists, e.g drilling brick, hand sanding, laying loft insulation.
  - Two point strap and adjustable nose clip for optimum fit.
  - Foam nose piece for extra comfort.
  - Colour coded straps for easy identification
- 
- Valve reduces effort by making it easier to exhale.
  - Protection against low level fine dust, oil or water based mists, e.g drilling brick, hand sanding, laying loft insulation.
  - Two point strap and adjustable nose clip for optimum fit.
  - Foam nose piece for extra comfort. Colour coded straps and valve for easy identification



AV13030



AV13031/AV13032



AV13033

- Protection against moderate level fine dust, oil or water based mists, e.g sanding hardwoods/MDF, mixing plaster/cement.
- Two point strap and adjustable nose clip for optimum fit.
- Foam nose piece for extra comfort.
- Colour coded straps for easy identification



AV13034

- Valve reduces effort by making it easier to exhale.
- Protection against moderate level fine dust, oil or water based mists, e.g sanding hardwoods/MDF, mixing plaster/cement.
- Two point strap and adjustable nose clip for optimum fit.
- Foam nose piece for extra comfort.
- Colour coded straps for easy identification



AV13036

Item Number	Item Description	EAN No	Commodity code	Carton Qty
AV13030	Avit Premium Disposable Odour Mask - P1 With Valve	5013969991703	55039000	
AV13031	Avit Disposable Mask P1 - Twin Pack	5013969991710	55039000	
AV13032	Avit Disposable Mask P1 - Box Of 20	5013969991727	55039000	
AV13033	Avit Premium Disposable Mask - P1 With Valve	5013969991734	55039000	
AV13034	Avit Disposable Mask P2 - Twin Pack	5013969991741	55039000	
AV13035	Avit Disposable Mask P2 - Box Of 20	5013969991758	55039000	
AV13036	Avit Premium Disposable Mask P2 - With Valve	5013969991765	55039000	

Technical product information	
Standards compliance	AV13030 to AV13033 - EN149: 2001 FFP1 NR AV13034 to AV13036 – EN149: 2001 FFP2 NR
User health and safety information	Avit respiratory protection masks are rated NR – Not re-usable. The masks therefore should be disposed of after a single use
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	Avit products are guaranteed for 1 year against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Taiwan

### Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
AV13030	150	50	135	14	180	65	210	56
AV13031	150	50	130	8	180	60	210	58
AV13032	150	50	130	8	150	140	160	236
AV13033	150	50	135	14	180	65	210	56
AV13034	150	50	130	8	180	60	210	58
AV13035	150	50	130	8	150	140	160	250
AV13036	150	50	135	14	180	65	210	56

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
AV13030	200	400	250	1138		
AV13031	200	400	250	1162		
AV13032	300	700	340	5540		
AV13033	200	400	250	1138		
AV13034	200	400	250	1162		
AV13035	300	700	250	5820		
AV13036	200	400	250	1138		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
AV13030	30	Blister	12	Backing card			466	Box
AV13031	28	Blister	12	Backing card			466	Box
AV13032			56	Box			820	Box
AV13033	30	Blister	12	Backing card			466	Box
AV13034	28	Blister	12	Backing card			466	Box
AV13035			56	Box			820	Box
AV13036	30	Blister	12	Backing card			466	Box