

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0016020078](#)  
**Status:** **Active**  
**Overview:** [C-Grid® Products](#)  
**Description:** SL™ Crimp Terminal, Series 70021, Male, with 0.76µm Selective Gold (Au) Plated Contact, 24-30 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-70021 \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">70021</a>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<a href="#">C-Grid® Products</a>
Packaging Alternative	<a href="#">16-02-0110 (Loose)</a>
Product Name	SL™
UPC	800753595972

**Physical**

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.094/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

**Solder Process Data**


Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Old Part Number	70021-0008
-----------------	------------

**Reference - Drawing Numbers**

Product Specification	PS-70021
Sales Drawing	SD-70021-0008



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[70021 Series](#)

**Use With**

[70066 Housing](#), [70107 Housing](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Insertion Tool	<a href="#">0011020022</a>
Extraction Tool	<a href="#">0011030036</a>
Hand Crimp Tool For SL™ Crimp Terminals	<a href="#">0638258800</a>
FineAdjust™ Applicator for Male	<a href="#">0639003400</a>

Crimp Terminal,  
24-30 AWG Wire  
FineAdjust™ 0639014500  
Applicator for Crimp  
Terminal, Male, 28  
AWG, 41 Strands/44  
AWG Wire  
T2 Terminator 0639103400  
Tooling Die

**Japan**

<b>Description</b>	<b>Product #</b>
Applicator for M21 1A Bench Press, 22-30 AWG Wire	<u>0570173000</u>
Hand Insertion Tool	<u>0570336000</u>

This document was generated on 05/04/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**