



PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Heavy Duty Cable Cutters
Catalogue number	3677, 3678, 3679
Date	18/04/2016

Range Description Ratchet cable cutter	
Features - 430007 <ul style="list-style-type: none">• Compact heavy duty cutter – for clean effortless cutting• High quality chrome molybdenum profiled steel blade - cuts cable up to 32mm diameter• Ratchet disengage lever - for quick cable loading• Integral locking mechanism - for safe storage• Designed to cut hard drawn copper cable, Aluminium cable or 200 pair communication cables• Not for use on steel or ACSR cable Features – T3678 <ul style="list-style-type: none">• High-grade special tool steel cutting jaws, forged and hardened for an extended working life• Heavy duty ratchet action for the effortless cutting of large diameter cable• Suitable for copper and aluminium cables up to 52 mmØ and SWA cable up to 36 mmØ.	

Features – T3679 <ul style="list-style-type: none"> • High-grade special tool steel cutting jaws, forged and hardened for an extended working life • Parrot-beak cutting jaws to prevent cable slippage • For large diameter copper and aluminium cables up to 27 mmØ • Not for use on steel or ACSR cable 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
430007	Ratchet cable cutter	5051074300072	82033000	
T3678	Heavy Duty Ratchet Cable Cutter	5013969961225	82033000	
T3679	Heavy Duty Cable Shears	5013969961218	82033000	

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship This tool contains working parts and cutting edges that will wear with use, such wear is not covered under the terms of the warranty
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
430007	75	25	270	779	130	30	330	835
T3678	120	27	320	868	142	33	400	942
T3679	140	30	545	1610	145	40	550	1785

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
430007	140	340	100	2605		
T3678	150	415	200	5824		
T3679	210	570	315	18640		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
430007	24	Blister	32	Backing card			100	Box
T3678	34	Blister	40	Backing card			172	Box
T3679	10	Bag	20	Card			790	Box