

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015975041](#)
Status: **Active**
Overview: Mini-Fit® TPA Plugs and Receptacles
Description: Mini-Fit® TPA Receptacle Housing, 4.20mm Pitch, Dual Row with Secondary Terminal Retention, 4 Circuits

Documents:

3D Model	Packaging Specification PK-30067-001 (PDF)
Drawing (PDF)	Test Summary TS-30067-001 (PDF)
Product Specification PS-45750-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-5556-003 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	30067
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.. Connector Position Assurance Mini-Fit® TPA Plugs and Receptacles
Overview	Mini-Fit® TPA
Product Name	800753595897
UPC	

Physical

Breakaway	No
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.671/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Old Part Number	30067-04A2
-----------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-30067-001
-------------------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/79/2015 (17 December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[30067](#) Series

Mates With

Plug [30068](#) , Straight Header [30069](#) , Right Angle Header [30070](#) , [44483](#)

Use With

[30071](#) Mini-Fit® Connector Position Assurance Key, [30072](#) Mini-Fit® TPA Key, [45750](#) Mini-Fit® Plus HCS Crimp Terminal

Product Specification
Sales Drawing
Test Summary

PS-45750-001, PS-5556-003
SD-30067-*
TS-30067-001

This document was generated on 06/03/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION