



TECHNICIAN TOOL KIT - ULTIMATE

Ultimate Technician Kit

Cat No: 52046987

UPC No: 769328113150

Description

Ultimate Technician Kit

Specifications

- Includes :
- PA1179 KT8 Round Cable Cutter
- PA1116 Data SureStrip® UTP/STP & Flat Satin Cutter/Stripper
- PA1257 LC-CST CATV "F" Coax Stripper
- PA1923 Untwist Tool
- PA1927 CATV "F" Flaring & Attachment Tool - RG6/RG6 QS
- PA1559 SealTite® Pro Compression Crimper
- PA1556 All-in-One Phone/Data tool
- PA3589 SurePunch® Pro punchdown tool
- PA4599 SurePunch® Pro detachable LED light
- PA4572 110 blade
- PA4591 Double 110 blade
- PA4573 66 blade
- PA4574 BIX blade
- PA4575 Krone LSA blade
- PA1543 LAN ProNavigator® tester & remote
- PA1573 Telephone Test Set & LAN Cable-Check™
- PA1902 RJ45 adapter
- PA1900 Can wrench
- (10) RJ22 handset plugs
- (10) PA9520 RJ11/12 plugs, stranded flat cable
- (10) PA9546 RJ45 plugs, Cat5e, solid, round cable
- (10) PA9644 CATV "F" RG6/RG6 QS connectors
- (2) PA901074 BNC-to-CATV "F" adapters
- PA4923 Ultimate Tool Bag

- Piano® plastic tackle box
- Replacement Part :
- PA1179 KT8 Round Cable Cutter
- PA1116 Data SureStrip® UTP/STP & Flat Satin Cutter/Stripper
- PA1257 LC-CST CATV "F" Coax Stripper
- PA1923 Untwist Tool
- PA1927 CATV "F" Flaring & Attachment Tool - RG6/RG6 QS
- PA1559 SealTite® Pro Compression Crimper
- PA1556 All-in-One Phone/Data tool
- PA3589 SurePunch® Pro punchdown tool
- PA4599 SurePunch® Pro detachable LED light
- PA4572 110 blade
- PA4591 Double 110 blade
- PA4573 66 blade
- PA4574 BIX blade
- PA4575 Krone LSA blade
- PA1543 LAN ProNavigator® tester & remote
- PA1573 Telephone Test Set & LAN Cable-Check™
- PA1902 RJ45 adapter
- PA1900 Can wrench
- (10) PA9520 RJ11/12 plugs, stranded flat cable
- (10) PA9546 RJ45 plugs, Cat5e, solid, round cable
- (10) PA9644 CATV "F" RG6/RG6 QS connectors
- (2) PA901074 BNC-to-CATV "F" adapters
- PA4923 Ultimate Tool Bag
- Size : 11.000 IN (279.000 MM) Width x 8.500 IN (216.000 MM) Length x 6.000 IN (152.000 MM) Depth
- Type : Ultimate
- Weight : 7.200 LB (3.300 KG)