


**STRAIGHT, INTERMEDIATE, BULKMTAD (R10)**

Code Ref. Ø F Ch L D lmax



**MINIATURE SERIES FOX**


2011A02	R10	3	M8x0.75	10	18.4	2	5
2011A01	R10	3.17	M8x0.75	10	18.4	2	5
2L11001	RL10	4	M11x1	13	28.6	2.5	11
2L11003	RL10	6	M13x1	16	31.2	4.5	12
2L11004	RL10	8	M15x1	17	33.9	6.5	13.5
2L11005	RL10	10	M17x1	20	37.8	8	17

**SERIES R**

2011001	R10	4	M13x1	16	34.0	3	11
2011002	R10	5	M14x1	17	33.5	4	8
2011003	R10	6	M15x1	17	33.5	5	10.5
2011004	R10	8	M17x1	20	40.0	7	17
2011005	R10	10	M20x1	24	44.5	9	17
2011006	R10	12	M22x1	25	50.5	11	23
2011007	R10	14	M24x1	27	53.0	12	22

**SINGLE RING (R13)**

Code Ref. Ø Ø 1 L L1 E E1




**SERIES R**

2012A02	R13	3	M5	17.2	9.0	9.0	7.0
2012A01	R13	3.17	M5	17.2	9.0	9.0	7.0
2012001	R13	4	M5	28.0	9.0	9.5	10.9
2012002	R13	4	1/8	32.0	15.0	14.0	11.5
2012003	R13	5	M5	28.8	9.0	9.5	12.0
2012004	R13	5	1/8	32.0	15.0	14.0	12.0
2012005	R13	6	1/8	32.0	15.0	14.0	13.5
2012006	R13	6	1/4	36.5	17.0	18.0	13.5
2012007	R13	8	1/8	37.5	15.0	14.0	15.5
2012008	R13	8	1/4	41.0	17.0	18.0	15.5
2012009	R13	8	3/8	42.0	20.0	21.0	15.5
2012010	R13	10	1/4	43.5	17.0	18.0	18.0
2012011	R13	10	3/8	47.0	20.0	21.0	18.0
2012013	R13	12	1/4	46.5	17.0	18.0	20.2
2012012	R13	12	3/8	50.5	20.0	21.0	20.2
2012014	R13	12	1/2	54.5	24.0	26.0	20.2

For the rods series D, see page 4.1/37

**DUAL RING (R14)**

Code Ref. Ø Ø 1 L L1 E E1



**SERIES R**

2013001	R14	4	M5	47.0	9.0	9.5	10.9
2013002	R14	4	1/8	50.0	15.0	14.0	11.5
2013003	R14	5	M5	48.0	9.0	9.5	12.0
2013004	R14	5	1/8	49.5	15.0	14.0	13.5
2013005	R14	6	1/8	50.0	15.0	14.0	13.5
2013006	R14	6	1/4	56.0	17.0	18.0	13.5
2013007	R14	8	1/8	60.0	15.0	14.0	15.5
2013008	R14	8	1/4	64.0	17.0	18.0	15.5
2013009	R14	8	3/8	63.0	20.0	21.0	15.5
2013010	R14	10	1/4	70.0	17.0	18.0	18.0
2013011	R14	10	3/8	73.0	20.0	21.0	18.0
2013013	R14	12	1/4	74.5	17.0	18.0	20.2
2013012	R14	12	3/8	79.5	20.0	21.0	20.2
2013014	R14	12	1/2	82.5	24.0	26.0	20.2

For the rods series D, see page 4.1/37