


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334670006](#)
Status: **Active**
Overview: MX64™ Sealed Connectors
Description: 2.54mm Pitch MX64™ Terminal, Gold (Au) Plating, 18-20 AWG, Left Reel Payoff, Also used with MX123™ Female Receptacle Housing

Documents:

Drawing (PDF)	Packaging Specification PK-31300-516 (PDF)
Product Specification PS-33468-001 (PDF)	Packaging Specification PK-31302-480 (PDF)
Application Specification AS-33468-001 (PDF)	RoHS Certificate of Compliance (PDF)
Packaging Specification PK-30907-759 (PDF)	



General

Product Family	Crimp Terminals
Series	33467
Application	Power
Comments	Left Reel Payoff
Crimp Quality Equipment	Yes
Overview	MX64™ Sealed Connectors
Product Name	MX123, MX64™
UPC	756054763391

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	0.225/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size AWG	18, 20
Wire Size mm²	N/A

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-33468-001
Packaging Specification	PK-30907-759, PK-31300-516, PK-31302-480
Product Specification	PS-33468-001
Sales Drawing	SD-33468-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Compliant

Search Parts in this Series

[33467 Series](#)

Use With

MX64™ Sealed Single Row Crimp Housing
[31403](#) , MX123™ Female Receptacle
Housing [34566](#) , [34576](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638114200
Manual Extraction Tool	0638131400
FineAdjust™ Applicator	0638673000

This document was generated on 06/13/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION