

## Mini DisplayPort to HDMI Adapter Cable - 3 m (10 ft.) - 4K 30Hz

StarTech ID: MDP2HDMM3MB



This 3-meter (10 ft.) Mini DisplayPort to HDMI® adapter cable offers a single-cable connection from your mDP equipped MacBook or Ultrabook™ laptop to an HDMI display or projector. The passive adapter supports video resolutions up to Ultra HD 4K and is Thunderbolt™ compatible, when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

### Astonishing picture quality

This adapter cable works with your 4K HDMI display and video source to ensure you it maintains it's astonishing picture quality, four times the resolution of 1080p, when converting Mini DisplayPort to HDMI.

The adapter is also backward compatible with lower resolution displays and video sources. With support for high-definition resolutions of 1080p and 720p, you can future-proof your existing setup for 4K video.

### Hassle-free setup

For the simplest and most discreet installation, this mDP to HDMI adapter connects directly from your Mini DisplayPort video source to the HDMI port on your display. It doesn't need a power source, unlike some converter dongles that require active power and separate video cabling.

### Clutter-free installation

At 3 m in length, this adapter cable delivers a direct connection that eliminates excess, to ensure a tidy, professional installation. For shorter or longer installations, we also offer a [1-meter mDP to HDMI cable \(MDP2HDMM1MB\)](#), a [2-meter mDP to HDMI cable \(MDP2HDMM2MB\)](#), and a [5-meter MDP to HDMI cable \(MDP2HDMM5MB\)](#) enabling you to choose the right cable length for your custom installation needs.

The MDP2HDMM3MB is backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Applications

- Connect a Mini DisplayPort computer to an HDMI display at your classroom desk or workstation
- Use in your boardroom or office workstations for installations requiring 3 meters (10 feet) of cable
- Install in your home workstation to make your DisplayPort computer compatible with your HDMI display
- Connect your mDP video source to a 4K HDMI display

## Features

- Astonishing video quality with support for video resolutions up to 4K at 30 Hz
- Reduce clutter with a 3 m adapter cable
- Avoid the hassle of converters that require additional cabling and power adapters with a plug-and-play cable adapter
- Supports HDMI 4K at 30 Hz
- Plug-and-play installation
- No power adapter required

**Technical Specifications**

Warranty	2 Years
Adapter Style	Adapter
Audio	Yes
Converter Type	Passive
Industry Standards	DPCP (DisplayPort Content Protection) HDCP (High Definition Content Protection) DisplayPort 1.2 HDMI 1.4
Audio Specifications	7.1 surround sound
Maximum Cable Length	118.1 in [3000 mm]
Maximum Digital Resolutions	4K x 2K @ 30 Hz
Supported Resolutions	4k x 2K (Ultra HD) 1920x1200 1920x1080 (1080p) 1280x720 (720p)
Wide Screen Supported	Yes
Connector A	1 - Mini-DisplayPort (20 pin) Male Input
Connector B	1 - HDMI (19 pin) Male Output
Humidity	10%-85%
Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-10°C to 70°C (14°F to 158°F)
Product Length	118.9 in [3020 mm]
Product Weight	4 oz [114 g]
Shipping (Package) Weight	4.4 oz [126 g]
Included in Package	1 - mDP to HDMI cable

Certifications, Reports and Compatibility

