

## Datasheet for part number CA3106E22-12PB13

Our Catalog Part Number: CA3106E22-12P-B-13

Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET

Product Datasheet		
Bayonet	Connector with bayonet coupling	
Shell Style	Plug, straight	
Endbell Style	Shielded connector with endbell for shielded braids and heat shrinkable boots	
Gender	Pin	
Shell Size	22	
Contact Arrangement	22-12	
Number of contacts	2 contacts size 8, 3 contacts size 16	
Contact Type	Solder Cup	
Contact Plating	Hard silver	
Shielding	yes	
Contact Rating at +20 °C (68 °F) (Size 15/15S/16/16S)	22 A	
Contact Rating at +20 °C (68 °F) (Size 60/100/8)	74 A	
Contact Resistance (Size 15/15S/16/16S)	6 mΩ	
Contact Resistance (Size 60/100/8)	1 mΩ	
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.	
Insulator Resistance	Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ	
Test Voltage	2500 Vrms	
Air and Creepage Paths (Min)	2,8 mm	
Ambient Temperature	Standard insulator material -55°/+125°C (-67/257°F)	
Safety Provisions	IP67 and IP68 (1 bar pressure after 12 hrs) acc. to DIN 40 050	
Salt Spray Resistance	500 hours salt spray resistant	
Mating Cycles	500 min	
Sep. Force per Contact (Size 15/15S/16/16S)	1,0 N	
Sep. Force per Contact (Size 60/100/8)	3,0 N	
Gage	For infos on Gage please see catalog VG95234, part 1	
Coupling Torque	Closing: 11 Nm max / Opening: 0,8 Nm min	
Contact Retention (Size 15/15S/16/16S)	35 N	
Contact Retention (Size 60/100/8)	80 N	
Shell Material	Aluminium alloy	
Shell Plating	Olive drab chromate over cadmium plating (conductive)	
Insulator and Grommet Material	CR-Elastomere	
Contact Material	Copper alloy	
Harnessing Info: Contact Cross-Section	See assembly instruction	
Harnessing Info: Insulator Diameter	See assembly instruction	

Specifications and dimensions subject to change.



## Datasheet for part number CA3106E22-12PB13

Our Catalog Part Number: CA3106E22-12P-B-13			
Brand: Cannon	Product Category: Circular	Product Line: CA Bayonet	Series: CA BAYONET

Product Datasheet	
Wire Stripping (Size 15/15S/16/16S)	6,2 mm
Wire Stripping (Size 60/100/8)	11,8 mm
General Info	All tests in accordance with VG95319 and/or if applicable with VG95210