

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002081001](#)
Status: **Active**
Overview: MLX™ Power Connectors
Description: MLX™ Crimp Terminal 42024, 14-20 AWG, Reel, Tin (Sn)

Documents:

[3D Model](#) [Product Specification PS-42022-0001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [42024](#)
 Application Power
 Crimp Quality Equipment Yes
 Overview [MLX™ Power Connectors](#)
 Packaging Alternative [02-08-1002 \(Loose\)](#)
 Product Name MLX™
 UPC 800753615878

Physical

Gender Female
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.344/g
 Packaging Type Reel
 Plating min - Mating 0.508µm
 Plating min - Termination 0.508µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.52-3.30mm
 Wire Size AWG 14, 16, 18, 20
 Wire Size mm² N/A

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number 42024-1A1

Reference - Drawing Numbers

Product Specification PS-42022-0001
 Sales Drawing SD-42024-****



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[42024 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hand Crimp Tool for Pin and Socket Crimp Terminals	0638116800
Extraction Tool FineAdjust™	0011010168 0639009800
Applicator for Crimp Terminals, 14-20 AWG Wire with 2.65-3.30mm Diameter Insulation	

Tooling Kit for Mini-Fit Compliant Pin Insertion	<u>0639107500</u>
T2 Terminator	<u>0639109900</u>
Tooling Die for Crimp Terminals, 14-20 AWG Wire	
FineAdjust™	<u>0639007500</u>
Applicator for Crimp Terminals, 14-20 AWG Wire with 2.08-2.50mm Diameter Insulation	
FineAdjust™	<u>0639009900</u>
Applicator for Crimp Terminals, 14-20 AWG Wire with 2.41-2.95mm Diameter Insulation	
T2 Terminator	<u>0639109800</u>
Tooling Die for Crimp Terminals, 14-20 AWG Wire	

This document was generated on 07/28/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION