

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0430252200

Status:

Active

Overview:

Micro-Fit 3.0™ Connectors

Description:

Micro-Fit 3.0™ Receptacle Housing, Dual Row, 22 Circuits

Documents:

- 3D Model

Drawing (PDF)

Product Specification PS-43045 (PDF)

Packaging Specification PK-43025-001 (PDF)
- Test Summary TS-43045-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Literature Order No

Product Name

UPC

Crimp Housings

43025

Power, Wire-to-Board, Wire-to-Wire

Polarized to Mating Part

Micro-Fit 3.0™ Connectors

987650-5984

Micro-Fit 3.0™

800753576735

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

22

Black

94V-0

Female

No

None

Yes

Polyester

2.160/g

2

Bag

No

3.00mm

Yes

No

-40°C to +105°C

Electrical

Current - Maximum per Contact

5.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing


Test Summary

PK-43025-001

PS-43045, RPS-43045-003, RPS-43045-004

SDA-43025-****, SDES-43025-1000

TS-43045-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

China RoHS

Green Image

Not Relevant

Search Parts in this Series

43025 Series

Mates With

43020 Micro-Fit 3.0™ Plug Housings, 43045
Micro-Fit 3.0™ Headers, 44242 Micro-Fit
3.0™ Test Plug

Use With

43030 , 45773 Micro-Fit 3.0™ Female Crimp
Terminals, 46235 Micro-Fit RMF™ Female
Crimp Terminals

This document was generated on 08/02/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION