

# Einhell

**EXPERT Plus**

**POWER X CHANGE**

## GE-HC 18 Li T Kit

Cordl. Multifunctional Tool-GT

Item No.: 3410805

Ident No.: 11013

Bar Code: 4006825601329

The cordless multi-functional tool GE-HC 18 Li T Kit is a powerful device to cut higher branches and high hedges from the ground, power network-independently and without effort. Due to the Einhell Power X-Change battery system, the multi-tool has a 18 V rechargeable battery with 3.0 Ah for extensive works. Thereby, the quality blade and chain by OREGON ensure a clean cross section. The automatic chain lubrication and the tool-free change of the chain allow simple operation. The laser-cut and diamond-ground knives of the hedge trimmer provide clean cutting results. The multi-tool can be adapted to any working situation by means of its various adjustment options.


### Features

- Battery system - Power X-Change
- Battery capacity control with 3 LEDs
- Battery can be used for other Power-X-Change products
- System high-speed charger included
- 90° pivotable attachment for effortless horizontal cuts
- Motor head tiltable by 7 settings
- Main handle tiltable by 4 settings
- Continuously adjustable telescopic aluminium handle (880-1820 mm)
- Additional adjustable handle with quick fastener
- Metal gearing for a long life
- OREGON quality blade and chain
- Toolless chain tensioning and chain change
- Oil tank for automatic chain lubrication
- Blade made of laser-cut and diamond-ground steel
- Sturdy cutter guard for storage and transportation



### Technical Data

- Battery capacity	3000 mAh
- Voltage d.c.	18 V
- Max. running time	40 min
- Charging time	1h
- Length chain saw bar	200 mm
- Chain cutting speed	3.76 m/s
- Max. cutting length hedge trimmer	400 mm
- Spacing between teeth	16 mm
- Cuts per minute	1700 min <sup>-1</sup>
- Number of accumulators	1 Pieces



### Logistic Data

- Tool weight	6.3 kg
- Gross Weight	8.2 kg
- Dimensions single packaging	1200 x 205 x 120 mm
- Pieces per export carton	3 Pieces
- Gross weight export carton	28 kg
- Dimensions Export Carton	1230 x 370 x 245 mm
- Container quantity (20"/40"/40"HC)	750   1551   1701



## Available as special accessories



18V 5,2 Ah Power-X-Change  
Battery  
Item No.: 4511357  
Bar Code: 4006825598865  
Einhell Accessory



18V 30min Power-X-Change  
Power Tools Accessory  
Item No.: 4512011  
Bar Code: 4006825587029  
Einhell Accessory



18V 1,5 Ah Power-X-Change  
Battery  
Item No.: 4511340  
Bar Code: 4006825590586  
Einhell Accessory



18V 3,0 Ah Power-X-Change  
Battery  
Item No.: 4511341  
Bar Code: 4006825590593  
Einhell Accessory



Ersatzschwert GC-EC 750 T  
Chain Saw Accessory  
Item No.: 4500168  
Bar Code: 4006825606348  
Einhell Grey



Ersatzkette GC-EC 750 T  
Chain Saw Accessory  
Item No.: 4500188  
Bar Code: 4006825606355  
Einhell Grey



18V 2,0 Ah Power-X-Change  
Battery  
Item No.: 4511395  
Bar Code: 4006825610369  
Einhell Accessory



18V 4,0 Ah Power-X-Change  
Battery  
Item No.: 4511396  
Bar Code: 4006825610376  
Einhell Accessory