

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0192770005**
Status: **Active**
Overview: Quixon™ Terminals
Description: Quixon Quick Disconnect, Avikrimp™ Style, Female, Fully Insulated Blue, 14-16 AWG, Loose

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E79133

General

Product Family Quick Disconnects
 Series [19277](#)
 Comments Low Insertion Force
 Crimp Quality Equipment Yes
 Insulated Fully
 MolexKits Yes
 Overview [Quixon™ Terminals](#)
 Product Name Avikrimp™, Quixon
 Type Quick Disconnect
 UPC 884982565203

Physical

Barrel Type Closed
 Color - Resin Blue
 Flammability 94V-2
 Gender Female
 Glow-Wire Compliant No
 Insulation Nylon (PA)
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 1.205/g
 Orientation Straight
 Packaging Type Bag
 Tab Thickness 0.41mm
 Tab Width 7.87mm
 Temperature Range - Operating -55°C to +105°C
 Wire Insulation Diameter 3.60mm
 Wire Size AWG 14, 16

Electrical


Voltage - Maximum 300V

Material Info

Old Part Number BB-5263-LIF

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
 Sales Drawing SD-19277-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[19277 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0640011100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051100

This document was generated on 03/07/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION