

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934443101](#)
Status: **Active**
Overview: ML-XT™ Sealed Connection System
Description: ML-XT™ Sealed 4 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

Drawing (PDF)	Packaging Specification 934430002 (PDF)
Application Specification 934430010 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Application Tooling Part Link	64003-8570
Overview	<u>ML-XT™ Sealed Connection System</u>
Product Name	ML-XT™
UPC	889056164559

Physical

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	7.823/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010
Packaging Specification	934430002
Sales Drawing	934430030



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[93444 Series](#)

Mates With

ML-XT™ Sealed 4 Circuit Plug Housing
[93445-3101](#)

Use With

ML-XT™ Male (Pin) Terminal [84524-0004](#)
 (Nickel), ML-XT™ Male (Pin) Terminal
[84524-0014](#) (Selective Gold), ML-XT™ 4
 Circuit Receptacle Wedgelock [93447](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description

Product #

Square "Din" Style 0640038570
Die Set for EXTreme
Guardian™
Power Receptacle
Terminals, 8 AWG
UL1028 or UL1283

This document was generated on 03/08/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION