

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0874370643](#)
Status: **Active**
Overview: Pico-SPOX™ Wire-to-Board Connector System
Description: 1.50mm Pitch Pico-SPOX™ Wire-to-Board Header, Surface Mount, Vertical, Shrouded, Nylon, 6 Circuits, Embossed Tape on Reel Packaging

Documents:

| | |
|--|---|
| 3D Model | Packaging Specification SPK-87437-001 (PDF) |
| Drawing (PDF) | Packaging Specification SPK-87438-001 (PDF) |
| Product Specification PS-87437-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

UL E29179

General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 87437 |
| Application | Signal, Wire-to-Board |
| MolexKits | Yes |
| Overview | Pico-SPOX™ Wire-to-Board Connector System |
| Product Name | Pico-SPOX™ |
| UPC | 822348438679 |


Physical

| | |
|--------------------------------|-----------------------|
| Breakaway | No |
| Circuits (Loaded) | 6 |
| Circuits (maximum) | 6 |
| Durability (mating cycles max) | 10 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Compliant | No |
| Guide to Mating Part | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Net Weight | 296.000/mg |
| Number of Rows | 1 |
| Orientation | Vertical |
| PCB Locator | No |
| PCB Retention | None |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 1.50mm |
| Plating min - Mating | 2.540µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Fully |
| Stackable | No |
| Temperature Range - Operating | -55°C to +105°C |
| Termination Interface: Style | Surface Mount |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 2.5A |
| Voltage - Maximum | 250V |

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[87437](#) Series

Mates With

[87439](#) Pico-SPOX™ Wire-to-Board Housing,
[87421](#) Pico-SPOX™ Crimp Terminal

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-87437-001, SPK-87438-001

PS-87437-001, RPS-87437, RPS-87437-001,

RPS-87437-200

SD-87437-001

This document was generated on 03/30/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION