

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5035661700](#)  
**Status:** **Active**  
**Overview:** FFC-FPC (SMT)  
**Description:** 0.30mm Pitch FPC Easy-On™ Housing Assembly, 17 Circuits, Mated Height 0.95mm

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-503566-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification SPK-503566-001 (PDF)</a>
<a href="#">Product Specification PS-503566-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

UL E29179

**General**

Product Family	FFC/FPC Connectors
Series	503566
Overview	FFC-FPC (SMT)
Product Name	Easy-On™
UPC	884982289208

**Physical**

Circuits (Loaded)	17
Circuits (maximum)	17
Color - Resin	Natural
Contact Position	Bottom
Durability (mating cycles max)	10
Entry Angle	Side Entry
Flammability	94V-0
Mated Height	0.95mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold over Nickel
Material - Resin	Polyester Alloy
Net Weight	27.878/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount
Wire/Cable Type	N/A


**Electrical**

Current - Maximum per Contact	0.2A
Voltage - Maximum	50V

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-503566-001
Packaging Specification	SPK-503566-001
Product Specification	PS-503566-001, RPS-503566-019, RPS-503566-022, RPS-503566-023, RPS-503566-024, RPS-503566-025, RPS-503566-027



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/39/2015 (15 June  
2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[503566 Series](#)

This document was generated on 03/29/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**