

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5019512410](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 0.50mm Pitch Easy-On™ Type FFC/FPC Connector, Vertical, Surface Mount, Copper Alloy Contacts, Gold Plating, 24 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-501951-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-501951-002 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family FFC/FPC Connectors
 Series [501951](#)
 Comments Actuator Color is Brown
 Overview [FFC-FPC \(SMT\)](#)
 Product Name Easy-On™
 UPC 822350672276


Physical

Circuits (Loaded) 24
 Circuits (maximum) 24
 Color - Resin White
 Contact Position N/A
 Durability (mating cycles max) 20
 Entry Angle Vertical
 Flammability 94V-0
 Mated Height 4.05mm
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Plating Termination Gold
 Material - Resin Liquid Crystal Polymer
 Net Weight 323.557/mg
 Number of Rows 1
 Orientation Vertical
 PCB Locator No
 PCB Retention Yes
 Packaging Type Embossed Tape on Reel
 Pitch - Mating Interface 0.50mm
 Pitch - Termination Interface 0.50mm
 Plating min - Mating 0.102µm
 Plating min - Termination 0.102µm
 Polarized to PCB No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -25°C to +85°C
 Termination Interface: Style Surface Mount
 Wire/Cable Type FFC/FPC

Electrical

Current - Maximum per Contact 0.4A
 Voltage - Maximum 50V AC (RMS)/DC

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[501951](#) Series

Mates With

Molex Premo-Flex FFC. Be sure to match like plating

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-501951-001

PS-501951-002, RPS-501951-001, RPS-501951-003,
RPS-501951-004, RPS-501951-005, RPS-501951-006,
RPS-501951-007, RPS-501951-009, RPS-501951-015,
RPS-501951-018, RPS-501951-019, RPS-501951-023
SD-501951-003, SD-501951-004, SD-501951-009

This document was generated on 03/07/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION