

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0561348000](#)
Status: **Active**
Overview: MicroClasp™ Wire-to-Board System
Description: 2.00mm Pitch Crimp Terminal 56134, Female, 22-26 AWG, Reel, Phosphor Bronze, for 51242/51353/51382 Housings

Documents:

[3D Model](#) [Packaging Specification SPK-56134-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification 5055960001 \(PDF\)](#)

General

Product Family Crimp Terminals
Series 56134
Application Signal
Crimp Quality Equipment Yes
Overview MicroClasp™ Wire-to-Board System
Product Name MicroClasp™
UPC 800756190532


Physical

Gender Female
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 36.000/mg
Packaging Type Reel
Plating min - Mating 0.889µm
Plating min - Termination 0.914µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.25-1.70mm
Wire Size AWG 22, 24, 26
Wire Size mm² N/A

Material Info

Reference - Drawing Numbers

Application Specification 5055960001
Packaging Specification SPK-56134-001
Product Specification RPS-51353-016, RPS-51382-015
Sales Drawing SD-56134-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[56134 Series](#)

Use With

[51242 Dual Row Crimp Housing](#), [51353 Dual Row Crimp Housing](#), [51382 Single Row Crimp Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	0011020022
Hand Crimp Tool	0638116300
Extraction Tool	0638132700
FineAdjust™	0639019600
Applicator for	

2.00mm Pitch
Female Crimp
Terminal
T2 Terminator 0639119600
for 2.00mm Pitch
Female Crimp
Terminal

Japan

Description **Product #**

Applicator for M211A 0574043000

Bench Press, 18-22

AWG Wire

Side-Feed Applicator 0574043200
for Full-Auto Machine

This document was generated on 08/15/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION