



Smart Wi-Fi Plug with Energy Monitoring

HS110


Highlights

- **Remote Access** – Control devices connected to the Smart Plug wherever you have Internet using the free Kasa app on your smartphone.
- **Scheduling** – Schedule the Smart Plug to automatically power electronics on and off as needed, like setting lights to come on at dusk or turn off at sunrise.
- **Energy Monitoring** – Analyze a device's real-time and historical power consumption.
- **Away Mode** – Turns your devices on and off at different times to give the appearance that someone is home.
- **Works with Amazon Alexa** – Control devices connected to the Smart Plugs just using your voice with Amazon Echo, Dot, Tap and other supported devices(sold separately).

Description


Easily turn on/off your appliance from anywhere in the world by a free App. You can also set some customized rules to turn it on/off as you scheduled.

Features




Ease of Use

- **Anytime, Anywhere** - The Smart Plugs make it easy to manage your household electronic devices anywhere in the world with a tap of your smartphone.
- **Schedule and Timer** - Deter bad guys by setting your lights to turn on and off on a schedule so it seems like you're home when you are actually away. And the count down timer gives you a peace of mind, which automatically switches off the running household appliances as your settings.



Compatibility

- **Works with Amazon Alexa** - You can pair the Smart Plugs with Amazon Echo, Dot, Tap and other supported devices for voice control.
- **Compatible with Android, iOS** - The free Kasa app lets you run them from any Android (4.1 and higher) or iOS (iOS 8 and higher) smartphone.



Energy Conservation

- **Real-time or historical** - You can efficiently conserve energy and save money while using the Smart Plugs to control your space heaters and fans. The Smart Plug tracks your device's power consumption in real-time, and has weekly and monthly summaries.

Specifications

Working Status

- **Input voltage:** 100 - 240V~, 50/60Hz, 13A
- **Output voltage:** 100 - 240V~, 50/60Hz, 13A
- **Maximum Load:** 13A
- **Maximum Power:** 2.2W

Network

- **Protocol:** IEEE 802.11b/g/n
- **Wireless Type:** 2.4GHz, 1T1R
- **System Requirements:** Android 4.1x or higher, iOS 8 or higher



For more information, please visit

<http://www.tp-link.com/uk/products/details/?model=HS110>

or scan the QR code left

Specifications are subject to change without notice. TP-LINK is a registered trademark of TP-LINK Technologies CO., Ltd. Other brands and product names are trademarks or registered trademarks of their respective holders. No part of the specifications may be reproduced in any form or by any means or used to make any derivative such as translation, transformation, or adaptation without permission from TP-LINK Technologies CO., Ltd.

General

- **Package Contents:** Smart Plug HS110, Quick Start Guide
- **Certifications:** RoHS, CE
- **Material:** PC
- **Buttons:** Power button, Settings button
- **Operating Temperature:** 0 °C ~ 40 °C (32°F ~ 104°F)
- **Operating Humidity:** 10%~90%RH, Non-condensing
- **Weight:** 131.8g
- **Dimensions (H x W x D):** 3.9 x 2.6 x 2.3 in. (100.3 x 66.3 x 58 mm)

www.tp-link.com