

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0526100833
Status: Active
Overview: FFC-FPC (SMT)
Description: Easy-On™ Type FFC/FPC Connector, Vertical, Surface Mount, ZIF Receptacle, 8 Circuits, High Barrier Packaging

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-52610-032 \(PDF\)](#)
[Packaging Specification SPK-52610-003 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family FFC/FPC Connectors
Series 52610
Overview FFC-FPC (SMT)
Product Name Easy-On™
UPC 887191316024

Physical

Circuits (Loaded) 8
Color - Resin Natural
Contact Position N/A
Durability (mating cycles max) 30
Entry Angle Vertical
Flammability 94V-0
Mated Height 5.75mm
Material - Metal Phosphor Bronze
Material - Plating Mating Silver, Tin-Bismuth
Material - Plating Termination Silver, Tin-Bismuth
Material - Resin Nylon
Net Weight 453.700/mg
Number of Rows 1
Orientation Vertical
PC Tail Length 2.00mm
PCB Locator No
PCB Retention None
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 1.00mm
Pitch - Termination Interface 1.00mm
Polarized to PCB No
Stackable No
Temperature Range - Operating -40°C to +85°C
Termination Interface: Style Surface Mount
Wire/Cable Type FFC/FPC


Electrical

Current - Maximum per Contact 1.0A
Voltage - Maximum 125V

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-52610-003



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

52610 Series

Mates With

<a href="http://www.molex.com/product/
premo_flex_ffc-fpc.html">Molex Premo-Flex
FFC. Be sure to match like plating

Product Specification

Sales Drawing

PS-52610-032, RPS-52610-075, RPS-52610-076,
RPS-52610-079
SD-52610-048, SD-52610-049

This document was generated on 03/03/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION