



# AV1200

Gigabit Powerline ac Wi-Fi Kit

TL-WPA8630 KIT

## Highlights

- **AC1200** – Deliver combined Wi-Fi speeds of up to 1200Mbps, ensuring optimal productivity and uninterrupted entertainment
- **HomePlug AV2** – Providing users with ultra-fast data transfer speeds of up to 1200Mbps, perfect for bandwidth-intensive activities
- **2X2 MIMO** – Establishes multiple simultaneous connections for you to enjoy higher powerline speeds and greater stability
- **Wi-Fi Clone Button** – Copy the network name (SSID) and password of your main router with the touch of a button to expand your network
- **Auto-Sync** – Easily add additional extenders to your powerline network, change from any device will be implemented on all network devices




Dual Band  
2.4 & 5 GHz



300Mbps+  
867Mbps



1200Mbps  
HomePlug AV2



Gigabit  
Ports



Plug & Play



Wi-Fi  
Clone



Wi-Fi  
Auto-Sync



tpPLC  
App



ANDROID APP ON  
Google play

# Features

## Speed

- Wireless AC Standard – Dual-band Wi-Fi speeds of 300Mbps on the 2.4GHz band and 867Mbps on the 5GHz band
- HomePlug AV2 – Provides up to 1200Mbps high-speed data transmission over a home's existing electrical wiring, making it ideal for HD video streaming and online gaming
- Multiple Gigabit Ports – Three gigabit ethernet ports allows you to connect game consoles, smart TVs, or media receivers to the Internet

## Reliability

- 2X2 MIMO with Beamforming – Establish simultaneous connections, providing more stable connections and expansive coverage

## Range

- Expansive Coverage – Utilizes any household powercircuit to deliver data over distances of up to 300 meters

## Security

- Pair Button – Provides a connection with 128-bit AES encryption, at the touch of "Pair" button

## Ease of Use

- Wi-Fi Clone – Allows powerline extenders to copy the network name (SSID) and password from your router with one simple touch
- Wi-Fi Auto-Sync – Automatically adopts Wi-Fi settings from your existing powerline network
- TP-LINK tpPLC – Allows you to easily manage your network using the intuitive tpPLC App or the tpPLC Utility
- Plug, Pair, and Play – Set up your powerline network in minutes

# Specifications

---

## Hardware

---

- **Transmission Speeds:** Powerline: up to 1200 Mbps  
Ethernet: 10/100/1000Mbps
- **Standards and Protocols:** HomePlug AV2, IEEE 1901, IEEE 802.3, IEEE 802.3u, IEEE 802.11b/g/n 2.4GHz, IEEE 802.11a/ac 5GHz
- **Interface:** 3 Gigabit Ethernet Ports
- **Plug Type:** UK
- **Button:** Pair, Reset, LED On/Off, Wi-Fi Clone
- **LED Indicator:** Power, Powerline, Ethernet, 2.4G Wi-Fi, 5G Wi-Fi
- **Item Dimensions (W x D x H):** 5.5 x 2.7 x 1.8 in. (140.6 x 68 x 45mm)
- **Packing Dimensions (W x D x H):** 9.1 x 7.5 x 3.9 in. (230x190x100 mm)
- **Access Methods:** CSMA/CA channel-access schemes
- **Frequency Band:** 2 MHz to 67.5 MHz
- **IGMP:** IGMP v1/v2/v3
- **Power Consumption:** Maximum: 10.8 W (230V/50Hz)  
Standby: 5W (230V/50Hz)
- **Range:** 300 meters in house
- **Compatibility:** Compatible with all HomePlug AV & AV2 Standard Powerline adapters

## Software

---

- **Modulation Technology:** OFDM
- **Security:** 128-bit AES Encryption
- **Quality of Service (QoS):** ToS  
Supports up to 4-level type QoS  
Support up to 8-level VLAN priority field

## Others

---

### Package Contents

- AV1200 Gigabit Powerline ac Wi-Fi Kit: TL-WPA8630 & TL-PA8010P
- 2-meter CAT.5e Ethernet Cable \* 2
- Quick Installation Guide

### Certification

- CE, RoHS

### System Requirements

- Windows 10/8.1/8/7/Vista/XP, Mac OS, Linux<sup>1</sup>


### Environment

- Operating Temperature: 0°C ~ 40°C (32°F ~ 104°F)
- Storage Temperature: -40°F ~ 158°F (-40°C ~ 70°C)
- Operating Humidity: 10% ~ 90% non-condensing
- Storage Humidity: 5% ~ 90% non-condensing


---

<sup>1</sup>Utility currently supports Windows 8/7/Vista/XP and Mac OS X (10.7 and later) operating system.

# Diagrams



## PLUG & PLAY IN SECONDS!



# Others

## Ideal to use with



- AC1900 Wireless Dual Band Gigabit Router Archer C9



- AC1750 Wireless Dual Band Gigabit Router Archer C8

## Similar Products



- AV1200 Gigabit Passthrough Powerline Starter Kit TL-PA8010P KIT



- AV500 Powerline ac Wi-Fi Kit TL-WPA4530 KIT

[www.tp-link.com](http://www.tp-link.com)

Specifications are subject to change without notice. TP-LINK is a registered trademark of TP-LINK TECHNOLOGIES CO., LTD. Other brands and product names are trademarks or registered trademarks of their respective holders. No part of the specifications may be reproduced in any form or by any means or used to make any derivative such as translation, transformation, or adaptation without permission from TP-LINK TECHNOLOGIES CO., LTD.

<sup>1</sup> Actual data will vary because of the network conditions and environment factors.

**TP-LINK®** AV1200 Gigabit Powerline ac Wi-Fi Kit **TL-WPA8630 KIT**