

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0016020078](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: SL™ Crimp Terminal, Series 70021, Male, with 0.76µm Selective Gold (Au) Plated Contact, 24-30 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	70021
Application	Signal
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-0110 (Loose)
Product Name	SL™
UPC	800753595972

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.094/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	70021-0008
--------------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-70021-0008
---------------	---------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[70021 Series](#)

Use With

[70066 Housing](#), [70107 Housing](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	0011020022
Extraction Tool	0011030036
Hand Crimp Tool For SL™ Crimp Terminals	0638258800
FineAdjust™ Applicator for Male	0639003400

Crimp Terminal,
24-30 AWG Wire
FineAdjust™ 0639014500
Applicator for Crimp
Terminal, Male, 28
AWG, 41 Strands/44
AWG Wire
T2 Terminator 0639103400
Tooling Die

Japan

Description	Product #
Applicator for M21 1A Bench Press, 22-30 AWG Wire	<u>0570173000</u>
Hand Insertion Tool	<u>0570336000</u>

This document was generated on 09/20/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION