

# LCD COLOUR MONITOR

## Model No. LM413

4" TFT LCD Colour Monitor with Digital LED Backlight Panel, Metal Case. 2 x Composite video inputs. Video Output. With Screen protector. Other sizes available.



### Main Features:

- Resolution: 960 x 240 - 230400 pixels.
- Picture Ratio: 4:3
- Brightness: 290 cd/m2. LED Back Light.
- Contrast Ratio: 250:1
- Digital Panel with LED Back light.
- Mounting: "C" mount in bottom.
- Output: Video and Audio via Headphone.
- Aluminium cabinet finished in Black.
- Easy to use controls.
- Inputs: 2 x Composite, Audio.
- LCD Panel Screen Protector.

The LM413 with TFT active matrix technology, Digital Panel and LED Backlight offers a sharp and high contrast display. With a metal case, it makes it ideal for rugged applications. With universal application potential, the LM413 is ideal for Surveillance Systems, Reverse Monitoring Systems and Multimedia Video applications. An audio input enables sound reception via headphones. A "C" mount thread in the bottom of the unit is for easy mounting.

### SPECIFICATIONS:

- Active area: 82.08 x 61.56 (WxH)mm. • 262K Colours. • PAL and NTSC Auto.
- Response Time: 3/7ms (Tr/Tf). • Viewing angle: Left/Right: 75°, Up:60°, Down:70°.
- Controls: Front: Brightness, Colour, Volume, On/Off switch.
- Side Controls: Video 1/2 switch. • Dot Pitch: 0.264 x 0.171.
- Power Source: 12V DC, 135mAmp, 1.62 Watts approx. Voltage range: DC 9.0 ~ 13V.
- Dimensions: 139 x 115 x 36. Carton: 195 x 52 x 143 (WxHxD)mm.
- Weight: Unit: 0.30Kgms, Carton: 0.41Kgms. • Temp: Operation: 0°C ~ 60°C, Storage: -20 ~ 70°.

**Connections:** Input: Video 1 & 2: Phono socket. Audio: Phono socket. Output: Video Phono socket. Headphone: 3.5mm socket. DC input: 2.1mm socket.

**Standard accessories:** None. **Optional:** AC adapter.

- All information correct at time of going to press. Design and specification are subject to change without prior notice. E&EO

## **Product Shop International Ltd**

PO Box 5503, Newbury, Berkshire, RG14 6YP. UK

e-mail: sales@productshop.co.uk Website www.productshop.co.uk

Tel: +44 (0) 844 800 4433 Fax: +44 (0) 844 800 9876

Registered office: As above. Registered No. 3852764 VAT No. GB 727 0478 29