

400A Digital Clamp Meter



General Characteristics

Power	: AAA 1.5V × 3
LCD Size	: 38mm × 24mm
Product Colour	: Orange and Grey
Product Net Weight	: 231.7g
Product Size	: 220mm × 75mm × 40mm
Standard Accessories	: Batteries, Test Lead

Specifications:

Basic Functions	Range	Best Accuracy
AC Current (A)	40A/400A	±(2.5%+5)
DC Current (A)	40A/400A	±(2.0%+3)
AC Voltage (V)	4V/40V/400V/600V	±(1.2%+5)
DC Voltage (V)	400mv4V/40V/400V/600V	±(0.8%+1)
Resistance (Ω)	400Ω/4kΩ/40kΩ/400kΩ/4MΩ/40MΩ	±(1.0%+2)
Capacitance (F)	40nF/400nF/4μF/40μF/400μF/4mF/40mF	±(4.0%+5)
Frequency(HZ)	10Hz-1MHz	±(0.1%+4)
Temperature(°C)	-40°C to 1000°C	±(1.0%+3)
Temperature(°F)	-40°F to 1832°F	±(1.0%+6)
Special Functions		
Display Count		4000
Auto Range		√
Jaw Capacity		30mm
True RMS		√
Diode	Around 3V	√
NCV		√
Auto Power Off	Around 15 Minutes	√
Continuity Buzzer		√
Low Battery Indication	≤3.6V	√
Data Hold		√
Zero Mode		√
LCD Backlight		√
Input Protection		√
Input Impedance for DCV	≥10MΩ	√

Part Number Table

Description	Part Number
400A Digital Clamp Meter	72-3510

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

